

Building Value in Air.

Refer to:

Installation Instructions for FD, DFD, DFD-X, & FD-X Series" (Part number 481324)

or

"Installation Instructions for FSD-XXX, DFD-XXX, & SSFSD-XXX Series Fire & Combination Fire Smoke Dampers' (Part number 481318)

or

"Installation Instructions for OFSD, ODFD, OFD, AND OSSFD Series Dampers' (Part number 461337) for additional details

Document Number 468502

Duct-Sleeve Connection Installation Instruction Supplement

"UL CLASSIFIED (see complete marking on product)"

"UL CLASSIFIED to Canadian safety standards (see complete marking on product)"

Standards UL 555 & 555S

Classifications Filed at UL under Listing #R13317



These instructions describe an alternate breakaway connection between a fire damper or combination fire smoke damper sleeve and an adjoining piece of ductwork. This alternate connection is covered under the UL certification of the damper. These instructions apply to a connection between a manufactured flange system by Ductmate, Dyn-o-mate, Ward, or Nexus and a TDC or TDF flange system.

- 1. Install the manufactured flange system onto the damper sleeve per the manufacturer's instructions.
- 2. To seal the two flange systems together Neoprene or Butyl gasket may be applied to the mating surfaces.
- 3. Align the two flange systems together. An optional 3/8 in. (9mm) bolt and nut may be used in the corners to help with the alignment. These bolts and nuts do not have to be removed.
- 4. Install the metal cleat (see Figure 1) or #10 tek screw (see Figure 2), approximately equally spaced, per the schedule described below:
 - Width or height less than 24 in. (610mm); use one cleat or screw per side
 - Width or height 24 in. (610mm) to less than 36 in. (914mm); use 2 cleats or screws per side
 - Width or height 36 in. (914mm) to less than 54 in. (1372mm); use 3 cleats or screws per side
 - Width or height 54 in. (1372mm) to less than 72 in. (1829mm); use 4 cleats or screws per side
 - Width or height 72 in. (1829mm) or greater; use 5 cleats or screws per side.




Figure 1

Phone: (715) 359-6171 • Fax: (715) 355-2399 • E-mail: gfcinfo@greenheck.com • Website: www.greenheck.com