Installation, Operation and Maintenance Manual

Please read and save these instructions for future reference. Read carefully before attempting to assemble, install, operate or maintain the product described. Protect yourself and others by observing all safety information. Failure to comply with these instructions will result in voiding of the product warranty and may result in personal injury and/or property damage.

WARNING

Disconnect power and observe proper lockout tagout procedures per OSHA Regulation, Title 29 Code of Federal Regulations Part 1910.147 & 1910.333.

NOTE


If fan is connected to electrical source via rigid connection, a qualified electrician will need to change the rigid connection to a flexible connection long enough per local electrical codes to allow for fan movement.


PARTS LIST		
Qty	Description	Part #
2	Latch Catch	758743
2	Latch	453116
2	5/16 inch-18 x .75 weld stud	415160
2	5/16 inch-18 nut	415456
4	#10-12 X .75 sheet metal screw	417393

Note: Hinged Curb Latch Kit can be applied to sidewall and roof mounted upblast fans.

Installation

- 1. Locate latch catch, 5/16 inch-18 x .75 weld stud and 5/16 inch-18 nut. Place latch catch on the inside of the fan curb cap and align top-most hole of the latch catch with the pre-punched hole on the curb cap. See Figure 1.
- 2. Insert 5/16 inch-18 x .75 weld stud through the latch catch and fan curb cap hole.
- 3. Ensure latch catch is perpendicular to curb cap, install and fully tighten 5/16 inch-18 nut.
- 4. Repeat steps 1 through 3 with second latch catch.





- 5. On lower tab of the latch catch, use two 1/8 inch holes to pilot drill into the roof curb. See Figure 2.
- 6. When pilot holes are drilled, bend the lower tab back and forth until it breaks free. Discard lower tab.
- 7. Place latch over the pilot holes and secure to the curb with self-drilling screws through the predrilled pilot holes. See Figure 3.

Figure 2




Figure 3

