






Selection Guide for Dampers



Type	Application	Model	BINDER TAB
 <p>Life Safety Dampers</p>	Fire	FD / DFDR Series FDR / DFDR Series OFD / ODFD Series	LIFE SAFETY DAMPER PRODUCTS
	Smoke	SMD / SMDR Series	
	Heavy Duty Smoke	HSD Series	LIFE SAFETY DAMPER PRODUCTS AND HEAVY DUTY/INDUSTRIAL
	Combination Fire-Smoke	FSD / FSDR Series CFSD Series OFSD Series GFSD Series	LIFE SAFETY DAMPER PRODUCTS
	Ceiling Radiation	CRD Series	
 <p>Control</p>	Commercial	VCD / VCDR Series VCDRM Series	CONTROL & BALANCING
	Heavy Duty / Industrial	HCD / HCDR Series	HEAVY DUTY/INDUSTRIAL
	Balancing	MBD / MBDR Series RBD / RBDR Series	CONTROL & BALANCING
	Insulated/Thermally Broken	ICD Series	
	Air Measuring	AMD / AMS Series	
	Face and Bypass Control	FBV / FBH Series	
Access Doors	Access Doors	HAD / CAD / RAD Series	ACCESS DOORS
Pressure Relief Doors	Pressure Relief Doors	PRAD / VRAD Series	
 <p>Backdraft</p>	Exhaust	BD Series EM-10 & EM-30 Series ES-10 & ES-30 Series WD-100 & WD-300 Series	BACKDRAFT
	Intake	EM-40 Series ES-40 Series WD-200 & WD-400 Series	
	Round	WDR / SSWDR Series	
	Heavy Duty/Industrial	HB Series	HEAVY DUTY/INDUSTRIAL AND BACKDRAFT
Relief Dampers	Heavy Duty/Industrial Pressure	HPR Series	HEAVY DUTY/INDUSTRIAL AND BACKDRAFT
	Barometric	BR Series	BACKDRAFT
 <p>Marine</p>	Fire	IMO-310, SSIMO-310	MARINE PRODUCTS
	Combination Fire Smoke	IMO-311, SSIMO-311	
 <p>Severe Environment</p>	Fire	SEDFD Series	LIFE SAFETY DAMPER PRODUCTS
	Combination Fire Smoke	SEFSD Series SEFSDR Series	
	Smoke	SESMD Series SESMDR-501 Series	
	Barometric	SEBR Series	BACKDRAFT
	Commercial Control	SEVCD Series	CONTROL & BALANCING
	Heavy Duty/Industrial Control	HCD Series HCDR Series	HEAVY DUTY/INDUSTRIAL
	Heavy Duty/Industrial Backdraft	HB Series	HEAVY DUTY/INDUSTRIAL AND BACKDRAFT
Tunnel Transit	Heavy Duty/Industrial	HTD Series	TUNNEL TRANSIT
Bubble-Tight	Heavy Duty/Industrial	HBTR Series	BUBBLE-TIGHT
Blast and Tornado	Heavy Duty/Industrial	HBS / HTOD Series	HEAVY DUTY/INDUSTRIAL

Selection Guide for Duct Heaters

 <p>Duct Heaters</p>	Duct Heaters	IDHB / IDHE Series	DUCT HEATERS
---	--------------	--------------------	--------------

Selection Guide for Louvers

Type	Application	Model
Florida Product Approved and Miami-Dade Qualified	Florida Product Approved	ESD-435X, ESD-635X, EHH-501X
	Miami-Dade Qualified	AFJ-601D, EACA-601D, EHH-601D, EHH-601DE, ESD-635D, ESD-635DE, ESS-502D, EVH-501D, EVH-660D, EHV-901D, EHH-601PD, ESD-635PD
Wind-Driven Rain	Vertical Blade	EVH-301, EVH-501, EVH-602
	Horizontal Blade	EHH-201, EHH-401, EHH-501, EHH-601, EHH-701
	Dual Module	EHV-901
Sightproof	Non-Drainable	SES-202
	Drainable Head	SEH-401
	Drainable Blade and Head	SED-401, SED-501
Drainable Blade	Drainable Blade	ESD-202, ESD-403, ESD-435, ESD-603, ESD-635
	Dual Drainable Blade	EDD-401, EDD-601, EHM-601
Drainable Head	J Blade	EDJ-401, EDJ-601, EDJ-430
	K Blade	EDK-430, EDK-402
	Intake / Discharge	ESID-430
Non-Drainable	J Blade	ESJ-202, ESJ-401, ESJ-602
	K Blade	ESK-402
Adjustable	Concealed Blade Linkage	EAD-401, EAD-601, EAD-635, EAH-401, EAH-690
Combination	Exposed Linkage	ECD-401, ECD-601
	Concealed Blade Linkage	EAC-401, EAC-601, EACN-601
	Airfoil Blade	EACA-601
	Concealed Blade Linkage and Concealed Actuator	EACC-401, EACC-601
	Gravity	GCE-402, GCI-402
Thinline	Frameless	ESU-153S, ESU-154S
	Narrow Profile Frame	ESJ-155, ESU-153, ESU-154
Acoustical	J Blade	AFJ-601, AFJ-801, AFJ-120
	Airfoil Blade	AFA-801
	Chevron Blade	AFS-120
Fabricated	Stationary Non-Drainable Blade	FSJ-402, FSJ-602
	Stationary Drainable Blade	FDS-402, FDS-602
	Adjustable Drainable Blade	FAD-402, FAD-635

Contact your local Greenheck Representative for a complete library of Greenheck Product Binders:

- Roof Mounted Fans and Gravity Ventilators
- Inline, Ceiling and Sidewall Fans
- Utility, Centrifugal and Radial Blowers
- Kitchen Ventilation Systems
- Dampers, Duct Heaters and Louvers
- Energy Recovery, Make-Up Air, Air Handlers, Fan Coils, Coils
- Fume Exhaust and Vektor® Laboratory Exhaust Systems

