

Service Disconnects for Vektor Laboratory Exhaust



Greenheck's Vektor laboratory exhaust systems are available with factory-mounted and wired service disconnect switches. These switches are available to disconnect power prior to inspection or performing field service work.



NEMA-3R, -4
Heavy Duty

NEMA-7, -9

NEMA-4

NEMA-3R

Note: NEMA-7, -9 are offered, but not factory-mounted

Safety Disconnect Switch Features

- Available in NEMA-3R
NEMA-4
NEMA-7, -9
- Available for 50 or 60 Hz power:
50 Hz: 190, 220, 380, 440 volt
60 Hz: 208, 230, 460, 575 volt
- Visible switch blades for positive "OFF" indication (some models)
- Padlock provision for the OFF position
- Horsepower rated for motor applications
- UL Listed electrical components

Vektor Service Disconnect Features and Options	Vektor-H Vektor-HS	Vektor-MH Vektor-MD Vektor-MS Vektor-CD
Toggle Type Switch	Yes	No
Heavy Duty Switch	Optional	Yes
Fusible Disconnect	Optional	Optional
Two-Speed Disconnect Switches	Optional	Optional
Disconnect Switches Wired for Y-Delta	Optional	Optional

Advantages:

- All factory-supplied single speed NEMA-3R and NEMA-4 disconnects ship factory-mounted and wired for motors up to 125 hp
- All wiring is enclosed in non-metallic, liquid-tight conduit
- All electrical connections are factory tested before shipment

As a result of our commitment to continuous improvement, Greenheck reserves the right to change specifications without notice.



Prepared to Support
Green Building Efforts

