

All louvers shown meet all International Building Code Requirements for the hurricane-prone region.

AMCA 540 & AMCA 550 Listed Louvers									
Model Name Max. Wind-load	Construction Description Dimensions – inches (mm)	AMCA Certifications	AMCA Listed	Miami-Dade County, FL NOA No.	Florida Product Approved No.	Florida Test Protocols	Minimum Opening	Maximum Section	Maximum Opening
							Dimensions – inches (mm)		
<a href="#">EVH-302</a>	3 in. (76) deep, extruded aluminum vertical rain resistant blade louver	Water, Air and Wind Driven Rain	AMCA 550, AMCA 540 Basic Level D	Not Applicable			12 W x 8 H (305 W x 203 H)	60 W x 96 H (1524 W x 2438 H)	Unlimited W x 96 H (Unlimited W x 2438 H)
<a href="#">EHV-550</a>	5.5 in. (140) deep, extruded aluminum horizontal front and vertical rear rain resistant blades		AMCA 550, AMCA 540 Enhanced Level E				8 W x 12 H (203 W x 305 H)	60 W x 96 H (1524 W x 2438 H)	Unlimited W x 96 H (Unlimited W x 2438 H)
<a href="#">EHV-901</a>	9 in. (229) deep, extruded aluminum horizontal front and vertical rear rain resistant blades						12 W x 12 H (305 W x 305 H)	60 W x 120 H (1524 W x 3048 H)	Unlimited W x 120 H (Unlimited W x 3048 H)
<a href="#">ESD-635D*</a> 150 PSF	6 in. (152) deep, extruded aluminum horizontal drainable blade louver	Water, Air	AMCA 550 (with factory attached VCD-40 damper in closed position), AMCA 540 Basic Level D and Enhanced Level E (with 0.125 blade/frame)	<a href="#">23-1013.08</a> EXP. 12/6/24	FL10088	TAS 201, TAS 202, TAS 203	12 W x 12 H (305 W x 305 W)	72 W x 144 H (1829 W x 3658 H)	Unlimited W x 144 H (Unlimited W x 3658 H)
<a href="#">ESD-635DE</a> 150 PSF	6 in. (152) deep, extruded aluminum horizontal drainable blade louver		AMCA 550 (with factory attached VCD-40 damper in closed position), AMCA 540 Basic Level D	<a href="#">20-0929.07</a> EXP. 2/4/26	FL19675		12 W x 12 H (305 W x 305 H)	48 W x 48 H (1219 W x 1219 H)	48 W x 48 H (1219 W x 1219 H)
<a href="#">EACA-601D</a> 110 PSF	6 in. (152) deep, extruded aluminum adjustable horizontal drainable blade louver		AMCA 550 (with Damper in closed position), AMCA 540 Basic Level D	<a href="#">23-0726.02</a> EXP. 12/5/28	FL16781		12 W x 16 H (305 W x 406 H)	60 W x 120 H (1524 W x 3048 H)	Unlimited W x 120 H (Unlimited W x 3048 H)
<a href="#">EHH-601D*</a> 150 PSF	6 in. (152) deep, extruded aluminum horizontal rain resistant blade louver	Water, Air and Wind Driven Rain	AMCA 550 (with factory attached VCD-40 Damper in closed position), AMCA 540 Enhanced Level E	<a href="#">23-1013.09</a> EXP. 11/1/24	FL10088	TAS-100(A): EVH-660D, EHH-601D (with VCD-40 damper blades closed)	12 W x 7 H (305 W x 178 H)	72 W x 144 H (1829 W x 3658 H)	Unlimited W x 144 H (Unlimited W x 3658 H)
<a href="#">EHV-550D</a> 100 PSF	5.5 in. (140) deep, extruded aluminum horizontal front and vertical rear rain resistant blades		AMCA 550, AMCA 540 Enhanced Level E	<a href="#">23-1101.03</a> EXP. 8/15/29	FL30297		12 W x 12 H (305 W x 305 H)	60 W x 96 H (1524 W x 2438 H)	Unlimited W x 96 H (Unlimited W x 2438 H)
<a href="#">EHV-901D</a> 130 PSF	9 in. (229) deep, extruded aluminum dual module rain resistant blade louver			<a href="#">23-1030.03</a> EXP. 7/28/26	FL19683		12 W x 12 H (305 W x 305 H)	60 W x 120 H (1524 W x 3048 H)	Unlimited W x 120 H (Unlimited W x 3048 H)
<a href="#">EVH-302D</a> 100 PSF	3 in. (76) deep, extruded aluminum vertical rain resistant blade louver			<a href="#">23-1101.05</a> EXP. 6/6/29	FL29694		12 W x 12 H (305 W x 305 H)	60 W x 96 H (1524 W x 2438 H)	Unlimited W x 96 H (Unlimited W x 2438 H)
<a href="#">EVH-501D</a> 130 PSF	5 in. (127) deep, extruded aluminum vertical rain resistant blade louver			<a href="#">23-1030.04</a> EXP. 8/6/25	FL19277		12 W x 12 H (305 W x 305 H)	120 W x 120 H, Limited to 70 ft <sup>2</sup> (3048 W x 3048 H, Limited to 6.5 m <sup>2</sup> )	Unlimited W x 120 H (Unlimited W x 3048 H)
<a href="#">EVH-660D</a> 150 PSF	6 in. (152) deep, extruded aluminum vertical rain resistant blade louver			<a href="#">22-0707.08</a> EXP. 10/4/27	FL16785		12 W x 12 H (305 W x 305 H)	48 W x 120 H or 60 W x 96 H or 96 W x 60 H (1219 W x 3048 H or 1524 W x 2438 H or 2438 W x 1524 H)	Unlimited W x 120 H (Unlimited W x 3048 H)

\*Also available in architectural shapes.