

Specifications

Display range of temperature	41°F to 95°F (5°C to 35°C)
Control range of temperature	44°F to 90°F (7°C to 32°C)
Load Rating	1 amp per terminal, 1.5 amp maximum all terminals combined
Swing (cycle rate or differential)	<ul style="list-style-type: none"> • Heating is adjustable from 0.2° to 2° • Cooling is adjustable from 0.2° to 2°
Power Source	<ul style="list-style-type: none"> • 18 to 30 VAC, NEC Class II, 50/60 Hz for hardwire • Battery power from 2-AA alkaline batteries
Operating Ambient	32°F to 105°F (0°C to +41°C)
Operating Humidity	90% non-condensing maximum
Dimension of Thermostat	4.7 in. W x 4.3 in. H x 0.9 in. D

