



Boost Efficiency. Simplify Operation.

Optional controls enable easy operation of Greenheck overhead HVLS fans while maximizing efficiency. Designed for convenience and versatility, Greenheck controls run one or multiple overhead HVLS fans with common communication protocols and are available with surface or recessed mounting kits.

KEYPAD CONTROL



- Cost-effective option offers complete control of an overhead fan system in a small, easy to operate, wall-mounted package.
- Allows user to operate 1, 3, 5, or 10 fans of the same model and size as a group, with all fans running at the same speed and direction.
- Provides full status monitoring capability and fault-logging, making this an excellent stand-alone control solution.
- Not compatible with DC-5 4.3 to 7-foot sizes or DM-3 5-foot size.

STANDARD TOUCHSCREEN CONTROL



- Sleek design fits in a standard 2x4 junction box and has an intuitive LCD screen.
- Allows user to operate 1, 3, 5, or 10 fans with any combination of models and sizes for increased flexibility.
- Touchscreen offers password protection along with advanced diagnostics for easy troubleshooting.
- Not compatible with DM-3 5-foot size.

ADVANCED TOUCHSCREEN CONTROL WITH BACnet®



- Premium option offers advanced capabilities for overhead fan system control with the simplicity of an intuitive LCD.
- Allows user to group or independently control 10 or 20 fans with any combination of models and sizes for optimum flexibility and convenience.
- Advanced touchscreen supports fan scheduling, password protection, advanced fan diagnostics, and the ability to communicate with a building management system (BMS) through BACnet® MS/TP.
- Available with optional temperature and humidity sensors to further boost occupant comfort.
- Not compatible with DM-3 5-foot size.