

SERIES XG-7550 PERFORMANCE DATA

Module	Neck Size	<i>fpm Neck Velocity</i>	300	400	500	600	700	800	1000	1200	
		<i>Pv</i>	.006	.010	.016	.022	.031	.040	.062	.090	
12 x 12	6 x 6	CFM	75	100	125	150	175	200	250	300	
		Pt	.013	.023	.036	.052	.071	.093	.145	.209	
		NC	<15	<15	<15	19	25	29	36	41	
		Throw	4-Way*	1-2-4	1-3-5	2-3-6	3-4-6	3-4-7	3-5-7	4-6-8	5-6-9
			4-Way	1-2-4	1-3-5	2-3-6	3-4-7	3-5-7	4-5-8	4-6-9	5-7-10
			3-Way	1-2-5	1-3-6	2-4-6	3-5-7	4-5-8	4-6-8	5-6-9	6-7-10
	2-Way		1-3-5	2-4-6	3-5-7	4-5-7	4-6-8	5-6-8	5-7-9	6-7-10	
	1-Way		2-3-5	2-4-6	3-5-7	4-5-7	4-6-8	5-6-9	6-7-10	6-7-10	
	8 x 8	CFM	135	180	220	265	310	355	445	535	
		Pt	.017	.031	.046	.067	.092	.121	.190	.275	
		NC	<15	<15	<15	20	27	32	39	45	
		Throw	4-Way*	1-2-5	2-3-7	3-4-8	3-5-8	4-6-9	5-7-10	6-8-11	7-8-12
			4-Way	1-2-5	2-4-7	3-4-8	4-5-9	4-6-10	5-7-11	6-8-12	7-9-13
			3-Way	1-2-6	2-4-8	3-5-9	4-6-9	5-7-10	5-8-11	7-9-12	8-9-13
2-Way	2-4-7		3-5-8	4-6-9	5-7-10	6-7-10	6-8-11	7-9-12	8-10-14		
1-Way	2-4-7		3-5-8	4-6-9	5-7-10	6-8-11	6-8-11	7-9-13	8-10-14		

**CEILING
DIFFUSERS**
**PERFORATED
CEILING DIFFUSERS**
XG-7500/XG-7550

SERIES XG-7550 PERFORMANCE DATA

Module	Neck Size	fpm Neck Velocity		300	400	500	600	700	800	1000	1200
		Pv		.006	.010	.016	.022	.031	.040	.062	.090
24 x 24	6 x 6	CFM		75	100	125	150	175	200	250	300
		Pt		.013	.023	.036	.052	.071	.093	.145	.209
		NC		<15	<15	<15	19	25	29	36	41
		Throw	4-Way*	1-2-4	1-3-5	2-3-6	3-4-7	3-5-7	4-5-8	5-6-9	5-7-9
			4-Way	1-2-4	1-3-6	2-4-7	3-4-7	3-5-8	4-6-8	5-7-9	6-7-10
			3-Way	1-2-5	1-3-6	2-4-7	3-5-7	4-6-8	4-6-9	5-7-10	6-7-11
			2-Way	2-3-5	3-4-6	3-5-7	4-5-8	4-6-8	5-6-9	6-7-10	6-8-11
	1-Way		2-3-6	3-4-6	3-5-7	4-6-8	4-6-8	5-6-9	6-7-10	6-8-11	
	CFM		135	180	220	265	310	355	445	535	
	Pt		.017	.031	.046	.067	.092	.121	.190	.275	
	NC		<15	<15	<15	20	27	32	39	45	
	Throw	4-Way*	1-3-5	2-4-7	3-4-8	4-5-9	4-6-10	5-7-10	5-8-11	7-9-13	
		4-Way	1-2-6	2-4-8	3-5-9	4-6-10	4-7-10	5-7-11	6-9-13	7-10-14	
		3-Way	1-2-6	2-4-8	3-5-9	4-6-10	5-7-11	6-8-11	7-9-13	8-10-14	
		2-Way	2-4-7	3-5-8	4-6-9	5-7-10	6-8-11	7-8-12	8-9-13	8-10-14	
		1-Way	2-4-7	3-5-9	4-6-9	5-7-10	6-8-11	7-8-12	8-9-13	8-10-15	
	10 x 10	CFM		210	280	345	415	485	555	695	835
		Pt		.023	.040	.061	.088	.120	.158	.247	.357
		NC		<15	<15	15	22	29	34	42	47
		Throw	4-Way*	1-3-7	3-5-9	4-6-10	4-7-11	5-8-12	6-9-13	8-10-14	9-11-16
			4-Way	1-3-7	2-5-9	4-6-11	5-7-12	5-8-13	6-9-14	8-11-16	9-12-17
			3-Way	1-3-8	2-5-10	4-7-11	5-8-12	6-9-13	7-10-14	9-11-16	10-12-18
			2-Way	3-5-9	4-6-10	5-8-12	6-9-13	7-10-14	8-10-15	9-12-16	10-13-18
	1-Way		3-5-9	4-6-11	5-8-12	6-9-13	7-10-14	8-11-15	10-12-17	11-13-18	
CFM		300	400	500	600	700	800	1000	1200		
Pt		.023	.040	.063	.090	.123	.160	.250	.360		
NC		<15	<15	15	23	30	35	44	50		
Throw	4-Way*	2-4-8	3-5-11	5-7-12	5-8-13	6-9-14	7-11-15	9-12-17	11-13-19		
	4-Way	2-4-8	3-6-11	4-7-13	6-8-15	7-10-16	7-11-17	9-13-19	11-15-21		
	3-Way	2-4-10	3-6-12	4-8-14	6-10-15	7-11-16	9-12-17	11-14-19	12-15-21		
	2-Way	3-6-11	5-8-12	6-10-14	8-11-15	9-12-16	10-12-18	11-14-20	12-15-21		
	1-Way	3-6-11	5-8-13	6-10-14	8-11-16	9-12-17	10-13-18	12-14-20	13-16-22		
14 x 14	CFM		410	545	680	815	955	1090	1360	1635	
	Pt		.023	.041	.064	.092	.126	.164	.255	.369	
	NC		<15	<15	16	24	31	37	46	51	
	Throw	4-Way*	2-4-9	3-6-13	5-8-14	6-9-16	7-11-17	8-13-18	10-14-20	13-16-22	
		4-Way	2-4-10	3-7-13	5-8-15	7-10-17	8-11-18	9-13-20	11-15-22	13-17-24	
		3-Way	2-4-11	3-7-14	5-9-16	7-11-17	9-13-19	10-14-20	12-16-22	14-17-25	
		2-Way	4-7-13	6-9-14	7-11-16	9-13-18	10-14-19	12-14-20	13-16-23	14-18-25	
1-Way		4-7-13	6-9-15	7-11-17	9-13-18	10-14-20	12-15-21	14-17-23	15-18-26		
CFM		535	710	890	1065	1245	1420	1780	2135		
Pt		.026	.046	.073	.104	.143	.186	.291	.419		
NC		<15	<15	16	24	33	39	49	53		
Throw	4-Way*	2-5-11	4-7-14	6-9-16	7-11-18	8-13-19	10-14-21	12-16-23	14-18-25		
	4-Way	2-5-11	4-7-15	6-9-18	7-11-19	9-13-21	10-15-22	12-18-25	15-19-27		
	3-Way	2-5-13	4-9-16	6-11-18	9-13-20	10-15-21	11-16-23	14-18-26	16-20-28		
	2-Way	4-8-14	7-10-17	8-13-18	10-14-20	12-15-22	13-17-23	15-18-26	17-20-29		
	1-Way	4-8-15	7-10-17	8-13-19	10-15-21	12-16-22	13-17-24	16-19-27	17-21-29		

CEILING
DIFFUSERS

PERFORATED
CEILING DIFFUSERS

XG-7500/XG-7550