

SP-CSP

Accessory Finishes

Roof Jack: RJ-4, RJ-6x9, RJ-10x10
Wall Cap: WC-10x3, WC-8x8, WC-18x8



Wall Louvered Discharge: WL-10x3, WL-18x6
Brick Vent: BEV-808, BEV-128, BEV-157



Wall Louvered Discharge: WL-10x3, WL-18x6



Wall Cap: WC-4, WC-6, WC-8
Flat Roof Flashing Flange: RFC-7
Roof Cap, Curb Mounted RCC-7
Curb Cap: GRS-10, GRS-12, GRS-16, GRS-20
Flashing Flange: GRSF-10, GRSF-12, GRSF-16, GRSF-20



Greenheck offers 27 powder coated finish options for hooded wall caps in the following models:
WC-4, WC-6, WC-8, WC-8x8, WC-18x8. Not available on model WC-10x3.

	Bone White	GF102		Ivory	031		Ascot White	GF120
	Dover White	AL202		Cambridge White	GF110		Herring Bone	GF107
	Sandstone	GF112		Pueblo Tan	GF116		Rawhide	AL215
	Smoke	GF104		Sierra Tan	GF118		Lindie Bronze	AL218
	Hampton Brown	GF105		Spartan Bronze	GF113		Classic Bronze	GF108
	Statuary Bronze	AL221		Dove Gray	AL213		Stone Gray	GF103
	Charcoal	AL214		Flat Black	044		Gloss Black	045
	Coronado Red	GF121		Terra Cotta	AL217		Hartford Green	AL208
	Capri Blue	GF106		Aegean Blue	AL204		Patina Green	GF114

The samples incorporated in this presentation are as close to production materials as color reproduction technology allows. Custom color matching is available upon request for quantity 35 or greater. Consult your Greenheck representative for additional cost associated with custom colors.