


Model: XG-SGRH Fixed Louver Face - Surface Mount

## XG-SGRH - Surface Mount



1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Finish Standard Finish: 01 White Optional Finish 02 Satin Silver 03 Black 28 Custom Color	XG-OBD - Steel Opposed Blade Damper XG-OBDA - Aluminum OBD Note: Dampers installed on security grilles will be rear operated	SH - Screw Holes SBR - Security Bars SAB - Steel Anchor Bar WAF - Welded Angle Frame  WSA - Welded Steel Angle BSA - Bolted Steel Angle LSA - Loose Steel Angle	<ul style="list-style-type: none"> <li>• Face Plate is 3/16" Thick</li> <li>• Dimension Type:     Nominal or Actual</li> <li>• X = Sleeve Length     (Must be specified)</li> <li>• Face Operated Damper     (Not Recommended)</li> </ul>

All Dimensions ±1/16"