



Hurricane-Prone Region Louver Products

All louvers shown meet some or all International Building Code Requirements for the hurricane-prone region.

AMCA 540 & AMCA 550 Listed Louvers									
Model Name Max. Wind-load	Construction Description Dimensions – inches (mm)	AMCA Certifications	AMCA Listed	Miami-Dade County, FL NOA No.	Florida Product Approved No.	Florida Test Protocols	Minimum Opening	Maximum Section	Maximum Opening
							Dimensions – inches (mm)		
SCV302	3 in. (76) deep, extruded aluminum vertical rain resistant blade louver	Water, Air and Wind Driven Rain	AMCA 550, AMCA 540 Basic Level D	Not Applicable	Not Applicable	Not Applicable	12 W x 8 H (305 W x 203 H)	60 W x 96 H (1524 W x 2438 H)	Unlimited W x 96 H (Unlimited W x 2438 H)
SCC550	5.5 in. (140) deep, extruded aluminum horizontal front and vertical rear rain resistant blades		AMCA 550, AMCA 540 Enhanced Level E				8 W x 12 H (203 W x 305 H)	60 W x 96 H (1524 W x 2438 H)	Unlimited W x 96 H (Unlimited W x 2438 H)
SCC901	9 in. (229) deep, extruded aluminum horizontal front and vertical rear rain resistant blades		AMCA 550, AMCA 540 Enhanced Level E				12 W x 12 H (305 W x 305 H)	60 W x 120 H (1524 W x 3048 H)	Unlimited W x 120 H (Unlimited W x 3048 H)
K8206AMD 110 PSF	6 in. (152) deep, extruded aluminum adjustable horizontal drainable blade louver	Water, Air	AMCA 550 (with Damper in closed position), AMCA 540 Basic Level D	23-0726.02 EXP. 12/5/28	FL16743	TAS 201, TAS 202, TAS 203 TAS-100(A): SCV501MD, SCV660MD (with VCD-40 damper blades closed)	12 W x 12 H (305 W x 305 W)	72 W x 144 H (1829 W x 3658 H)	Unlimited W x 144 H (Unlimited W x 3658 H)
K6746MD* 150 PSF	6 in. (152) deep, extruded aluminum horizontal drainable blade louver		AMCA 550 (with factory attached VCD-40 damper in closed position), AMCA 540 Basic Level D and Enhanced Level E (with 0.125 blade/frame)	23-1013.10 EXP. 12/6/24	FL10093		12 W x 12 H (305 W x 305 H)	48 W x 48 H (1219 W x 1219 H)	48 W x 48 H (1219 W x 1219 H)
K6746MDE 150 PSF	6 in. (152) deep, extruded aluminum horizontal drainable blade louver		AMCA 550 (with factory attached VCD-40 damper in closed position), AMCA 540 Basic Level D	20-0929.09 EXP. 2/4/26	FL19676		12 W x 16 H (305 W x 406 H)	60 W x 120 H (1524 W x 3048 H)	Unlimited W x 120 H (Unlimited W x 3048 H)
SCH601MD* 150 PSF	6 in. (152) deep, extruded aluminum horizontal rain resistant blade louver		AMCA 550 (with factory attached VCD-40 Damper in closed position), AMCA 540 Enhanced Level E	23-1013.11 EXP. 11/1/24	FL10093		12 W x 7 H (305 W x 178 H)	72 W x 144 H (1829 W x 3658 H)	Unlimited W x 144 H (Unlimited W x 3658 H)
SCC550MD 100 PSF	5.5 in. (140) deep, extruded aluminum horizontal front and vertical rear rain resistant blades	Water, Air and Wind Driven Rain	AMCA 550, AMCA 540 Enhanced Level E	23-1101.04 EXP. 8/15/29	FL30298	TAS-100(A): SCV501MD, SCV660MD (with VCD-40 damper blades closed)	12 W x 12 H (305 W x 305 H)	60 W x 96 H (1524 W x 2438 H)	Unlimited W x 96 H (Unlimited W x 2438 H)
SCC901MD 130 PSF	9 in. (229) deep, extruded aluminum horizontal front and vertical rear rain resistant blades		AMCA 550, AMCA 540 Enhanced Level E	23-1030.06 EXP. 7/28/26	FL19685		12 W x 12 H (305 W x 305 H)	60 W x 120 H (1524 W x 3048 H)	Unlimited W x 120 H (Unlimited W x 3048 H)
SCV302MD 100 PSF	3 in. (76) deep, extruded aluminum vertical rain resistant blade louver		AMCA 550, AMCA 540 Basic Level D	23-1101.06 EXP. 6/6/29	FL29695		12 W x 12 H (305 W x 305 H)	60 W x 96 H (1524 W x 2438 H)	Unlimited W x 96 H (Unlimited W x 2438 H)
SCV501MD 130 PSF	5 in. (127) deep, extruded aluminum vertical rain resistant blade louver		AMCA 550, AMCA 540 Enhanced Level E	23-1030.07 EXP. 8/6/25	FL19278		12 W x 12 H (305 W x 305 H)	120 W x 120 H, Limited to 70 ft ² (3048 W x 3048 H, Limited to 6.5 m ²)	Unlimited W x 120 H (Unlimited W x 3048 H)
SCV660MD 150 PSF	6 in. (152) deep, extruded aluminum vertical rain resistant blade louver		AMCA 550, AMCA 540 Enhanced Level E	22-0707.09 EXP. 10/4/27	FL16746		12 W x 12 H (305 W x 305 H)	48 W x 120 H or 60 W x 96 H or 96 W x 60 H (1219 W x 3048 H or 1524 W x 2438 H or 2438 W x 1524 H)	Unlimited W x 120 H (Unlimited W x 3048 H)

*Also available in architectural shapes.

January 2024

Copyright © 2024 The Airlite Company LLC