

All louvers shown meet some or all Florida and International Building Code Requirements for the hurricane-prone region.

Model Name Max. Wind-load	Construction Description Dimensions – inches (mm)	AMCA Certifications	AMCA Listed	Miami-Dade County, FL NOA No.	Florida Product Approved No.	Florida Test Protocols	Minimum Opening	Maximum Section	Maximum Opening
							Dimensions – inches (mm)		
<b>Miami-Dade Approved Louvers and Penthouses</b>									
<a href="#">K6746MD*</a> 150 PSF	6 in. (152) deep, extruded aluminum horizontal drainable blade louver	Water, Air	AMCA 550 (with factory attached VCD-40 damper in closed position), AMCA 540 Basic Level D and Enhanced Level E (with 0.125 blade/frame)	<a href="#">23-1013.10</a> EXP. 12/6/24	FL10093	TAS 201, TAS 202, TAS 203  TAS-100(A): SCV501MD, SCV660MD (with VCD-40 damper blades closed)	12 W x 12 H (305 W x 305 H)	72 W x 144 H (1829 W x 3658 H)	Unlimited W x 144 H (Unlimited W x 3658 H)
<a href="#">K6746MDE</a> 150 PSF	6 in. (152) deep, extruded aluminum horizontal drainable blade louver		AMCA 550 (with factory attached VCD-40 damper in closed position), AMCA 540 Basic Level D	<a href="#">20-0929.09</a> EXP. 2/4/26	FL19676		12 W x 12 H (305 W x 305 H)	48 W x 48 H (1219 W x 1219 H)	48 W x 48 H (1219 W x 1219 H)
<a href="#">K8206AMD</a> 110 PSF	6 in. (152) deep, extruded aluminum adjustable horizontal drainable blade louver		AMCA 550 (with damper in closed position), AMCA 540 Basic Level D	<a href="#">23-0726.02</a> EXP. 12/5/28	FL16743		12 W x 16 H (305 W x 406 H)	60 W x 120 H (1524 W x 3048 H)	Unlimited W x 120 H (Unlimited W x 3048 H)
<a href="#">SCC901MD</a> 130 PSF	9 in. (229) deep, extruded aluminum horizontal front and vertical rear rain resistant blades	AMCA 550, AMCA 540 Enhanced Level E	<a href="#">23-1030.06</a> EXP. 7/28/26	FL19685	12 W x 12 H (305 W x 305 H)		60 W x 120 H (1524 W x 3048 H)	Unlimited W x 120 H (Unlimited W x 3048 H)	
<a href="#">SCH601MD*</a> 150 PSF	6 in. (152) deep, extruded aluminum horizontal rain resistant blade louver	AMCA 550 (with factory attached VCD-40 damper in closed position), AMCA 540 Enhanced Level E	<a href="#">23-1013.11</a> EXP. 11/1/24	FL10093	12 W x 7 H (305 W x 178 H)		72 W x 144 H (1829 W x 3658 H)	Unlimited W x 144 H (Unlimited W x 3658 H)	
<a href="#">SCH601MDE</a> 150 PSF	6 in. (152) deep, extruded aluminum horizontal rain resistant blade louver	AMCA 540 Enhanced Level E	<a href="#">20-0929.08</a> EXP. 12/24/25	FL19673	12 W x 7 H (305 W x 178 H)		48 W x 48 H (1219 W x 1219 H)	48 W x 48 H (1219 W x 1219 H)	
<a href="#">SCC550MD</a> 100 PSF	5.5 in. (140) deep, extruded aluminum horizontal front and vertical rear rain resistant blades	Water, Air and Wind Driven Rain	AMCA 550, AMCA 540 Enhanced Level E	<a href="#">23-1101.04</a> EXP. 8/15/29	FL30298		12 W x 12 H (305 W x 305 H)	60 W x 96 H (1524 W x 2438 H)	Unlimited W x 96 H (Unlimited W x 2438 H)
<a href="#">SCV302MD</a> 100 PSF	3 in. (76) deep, extruded aluminum vertical rain resistant blade louver		AMCA 550, AMCA 540 Basic Level D	<a href="#">23-1101.06</a> EXP. 6/6/29	FL29695		12 W x 12 H (305 W x 305 H)	60 W x 96 H (1524 W x 2438 H)	Unlimited W x 96 H (Unlimited W x 2438 H)
<a href="#">SCV501MD</a> 130 PSF	5 in. (127) deep, extruded aluminum vertical rain resistant blade louver		AMCA 550, AMCA 540 Enhanced Level E	<a href="#">23-1030.07</a> EXP. 8/6/25	FL19278		12 W x 12 H (305 W x 305 H)	120 W x 120 H, Limited to 70 ft <sup>2</sup> (3048 W x 3048 H, Limited to 6.5 m <sup>2</sup> )	Unlimited W x 120 H (Unlimited W x 3048 H)
<a href="#">SCV660MD</a> 150 PSF	6 in. (152) deep, extruded aluminum vertical rain resistant blade louver		AMCA 550, AMCA 540 Enhanced Level E	<a href="#">22-0707.09</a> EXP. 10/4/27	FL16746		12 W x 12 H (305 W x 305 H)	48 W x 120 H or 60 W x 96 H (1219 W x 3048 H or 1524 W x 2438 H or 2438 W x 1524 H)	Unlimited W x 120 H (Unlimited W x 3048 H)
<a href="#">SCH601PD</a> 115 PSF	6 in. (152) deep, extruded aluminum horizontal rain resistant blade louvered penthouse	Not Applicable	Not Applicable	<a href="#">23-1026.09</a> EXP. 6/19/28	FL11357	Min. Throat W x L x Min. H 12 x 12 x 12 (305 x 305 x 305)	Max. Throat W x L x Max. H 84 x 108 x 84 (2134 x 2743 x 2134)	Max. Throat W x L x Max. H 84 x 108 x 84 (2134 x 2743 x 2134)	
<a href="#">K6746PD</a> 115 PSF	6 in. (152) deep, extruded aluminum horizontal drainable blade louvered penthouse			<a href="#">23-1026.10</a> EXP. 6/19/28	FL11357	Min. Throat W x L x Min. H 12 x 12 x 12 (305 x 305 x 305)	Max. Throat W x L x Max. H 84 x 108 x 84 (2134 x 2743 x 2134)	Max. Throat W x L x Max. H 84 x 108 x 84 (2134 x 2743 x 2134)	
<b>Florida Product Approved Louvers</b>									
<a href="#">K6744X*</a> Max. 200 PSF <sup>^</sup>	4 in. (102) deep, extruded aluminum horizontal drainable blade louver	Water, Air	AMCA 540 Basic Level D	Not Applicable	FL7708, FL35290	Standard: TAS 202	12 W x 9 H (305 W x 229 H)	120 W x 144 H Limited to 70 ft <sup>2</sup>  (3049 W x 3658 H Limited to 6.5 m <sup>2</sup> )	Unlimited W x 144 H or 120 W x Unlimited H  (Unlimited W x 3658 H or 3048 W x Unlimited H)
<a href="#">K6746X*</a> Max. 200 PSF <sup>^</sup>	6 in. (152) deep, extruded aluminum horizontal drainable blade louver		AMCA 540 Enhanced Level E		FL7708, FL35290		Welded: TAS 201, TAS 202, TAS 203		
<a href="#">SCH501X*</a> Max. 200 PSF <sup>^</sup>	5 in. (127) deep, extruded aluminum horizontal rain resistant blade louver	AMCA 540 Enhanced Level E	FL7708, FL35290		12 W x 7 H (305 W x 178 H)				

\*Also available in architectural shapes. ^Size/section dependent.