

HEAVY-DUTY GRILLES Selection Guide



Greenheck Model	Material Options		Blade Deflection			Front Blade Orientation		Width and Height Sizes			
	Steel	Aluminum	Adjustable	38 Degree	0 Degree	Horizontal	Vertical	Min Width (Inches)	Min Height (Inches)	Max Width (Inches)	Max Height (Inches)
Return											
XG-4500		X			X	X		6	4	144	144
XG-4500S	X				X	X		6	4	144	144
XG-4538		X		X		X		6	4	144	144
XG-4538S	X			X		X		6	4	144	144
XG-HDRH		X				X	X	6	4	144	144
Supply Double Deflection											
XG-H4504		X	X			X		6	4	144	144
XG-H4504S	X		X			X		6	4	144	144
XG-V4504		X	X				X	6	4	144	144
XG-V4504S	X		X				X	6	4	144	144
Supply Single Deflection											
XG-H4502		X	X			X		6	4	144	144
XG-H4502S	X		X			X		6	4	144	144
XG-V4502		X	X				X	6	4	144	144
XG-V4502S	X		X				X	6	4	144	144