



Model: XG-AFR-10	1" Slot - Non Insulated
XG-AFR-15	1 1/2" Slot - Non Insulated
XG-AFR-20	2" Slot - Non Insulated
XG-AFR-25	2 1/2" Slot - Non Insulated
XG-AFR-30	3" Slot - Non Insulated

XG-AFR - Return Hood Light Shield



Installation End View



3D View

1 - Slot			
Slot Width	Dim H	Dim W-1	Dim W-2
1"	2 1/2"	2 1/8"	2 5/8"
1 1/2"	2 1/2"	2 5/8"	3 1/8"
2"	2 1/2"	3 1/8"	3 5/8"
2 1/2"	2 1/2"	4 5/8"	5 1/8"
3"	2 1/2"	5 1/8"	5 5/8"

2 - Slot			
Slot Width	Dim H	Dim W-1	Dim W-2
1"	2 1/2"	5 1/16"	5 9/16"
1 1/2"	2 1/2"	6 1/16"	6 9/16"
2"	2 1/2"	7 1/16"	7 9/16"
2 1/2"	2 1/2"	10 1/16"	10 9/16"
3"	2 1/2"	11 1/16"	11 9/16"

1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 03 Black		15/16" Tee System 9/16" Tee System 9/16" Bolt Slot Tee System Hard Ceiling	<ul style="list-style-type: none"> Aluminum Construction Length 48" Field Cut to Fit Finish on interior only

All Dimensions ±1/16"