


STANDARD COLD DAMPER LOCATION IS RH  
ORDER OPTION 26 FOR LH

STANDARD HOT DAMPER LOCATION IS LH  
ORDER OPTION 26 FOR RH



—— Factory Piping  
- - - Field Piping By Others

**DDCD 240M**

(CDS) ATU\CONTROL DIAGRAMS\PNEUMATIC\

Unless Otherwise Specified:  
1. Dimensions Are In Inches.  
2. Tolerances Are:  
Fractions Decimals Angles  
±.X = .1  
±1/32 ±.XX = .02 ±1°  
±.XXX = .010

# Control Wiring Diagram

Direct Acting N.C. Cold RA N.O, Hot  
For Use With Mixing And Non Mixing Units

Phone: 715.359.6171  
Fax: 715.355.2399  
Parts : 800.355.5354  
gfcinfo@greenheck.com  
www.greenheck.com

N/A	F	Removed logo	7/8/21	CG
ECN. No.	Rev	Description	Date	Rev'd By:

DWN. BY	DG	DATE	11/07/05	DWG. NO.		REV.	
CHK'D BY	DG	SCALE	NTS	DDCD 240M		F	