



257N - No Xformer  
 257A - 120 / 24  
 257C - 277 / 24  
 257F - 240 / 24

Optional  
 Thermostat  
 (TB6980A1007)

3 — Open 1  
 4 — Close 1  
 1 — 24 VAC  
 2 — COM

Wiring Box

AC Supply  
 L1  
 L2(N)  
 Ground

— Factory Piping  
 - - - Field Piping By Others

Actuator-ML6161B2024, 90 Second.  
 Optional Transformer - 40 VA Min.

**DDCD 258**

(CDS) ATU\CONTROL DIAGRAMS\ELECTRIC\

# Control Wiring Diagram

Dual Duct Air Terminal Unit  
 Electric Actuator, Floating Type

Unless Otherwise Specified:  
 1. Dimensions Are In Inches.  
 2. Tolerances Are:  
 Fractions Decimals Angles  
 $\pm .X = .1$   
 $\pm 1/32 \quad \pm .XX = .02 \quad \pm 1^\circ$   
 $\pm .XXX = .010$

Phone: 715.359.6171  
 Fax: 715.355.2399  
 Parts : 800.355.5354  
 gfcinfo@greenheck.com  
 www.greenheck.com

N/A	F	Remove logo	7/7/21	CG
ECN. No.	Rev	Description	Date	Rev'd By:

DWN. BY	CLS	DATE	11/10/05	DWG. NO.		REV.	
CHK'D BY	DSG	SCALE	NTS	DDCD258		F	