



———— Factory Piping
----- Field Piping By Others

BPCD 316M

(CDS) ATU\CONTROL DIAGRAMS\PNEUMATIC\

Control Wiring Diagram

Unless Otherwise Specified:
1. Dimensions Are In Inches.
2. Tolerances Are:
Fractions Decimals Angles
 $\pm 1/32$ $\pm .X = .1$ $\pm 1^\circ$
 $\pm .XX = .02$ $\pm .XXX = .010$

RANC 3 - 8 PSI Pneumatic
Pressure Independent

Phone: 715.359.6171
Fax: 715.355.2399
Parts : 800.355.5354
gfcinfo@greenheck.com
www.greenheck.com

ECN. No.	Rev	Description	Date	Rev'd By:
N/A	C	Removed logo	7/12/21	CG
N/A	B	Update to new format	6/08/17	RE
N/A	A	Actuator Update	9/07/06	CLS

DWN. BY	CLS	DATE	9/07/06	DWG. NO.	BPCD 316M	REV.	C
CHK'D BY	RE	SCALE	NTS				