



—— Factory Piping
 - - - Field Piping By Others

BPCD 317M

(CDS) ATU\CONTROL DIAGRAMS\PNEUMATIC\

Control Wiring Diagram

RANO 3 - 8 PSI Pneumatic
 Pressure Independent

Unless Otherwise Specified:
 1. Dimensions Are In Inches.
 2. Tolerances Are:
 Fractions Decimals Angles
 $\pm 1/32$ $\pm .X = .1$ $\pm 1^\circ$
 $\pm .XX = .02$
 $\pm .XXX = .010$

Phone: 715.359.6171
 Fax: 715.355.2399
 Parts : 800.355.5354
 gfcinfo@greenheck.com
 www.greenheck.com

ECN. No.	Rev	Description	Date	Rev'd By:
N/A	C	Removed logo	7/12/21	CG
N/A	B	Update to new format	6/09/17	RE
N/A	A	Actuator Update	9/07/06	CLS

DWN. BY	CLS	DATE	9/07/06	DWG. NO.	BPCD 317M	REV.	C
CHK'D BY	RE	SCALE	NTS				