



———— Factory Piping
 - - - - Field Piping By Others

SRCD 414M

(CDS) ATU\CONTROL DIAGRAMS\PNEUMATIC\

Control Wiring Diagram

DANC 8 - 13 PSI Pneumatic
 Pressure Independent

Unless Otherwise Specified:
 1. Dimensions Are In Inches.
 2. Tolerances Are:
 Fractions Decimals Angles
 $\pm 1/32$ $\pm .X = .1$ $\pm 1^\circ$
 $\pm .XX = .02$
 $\pm .XXX = .010$

| ECN. No. | Rev | Description | Date | Rev'd By: |
|----------|-----|----------------------|---------|-----------|
| N/A | C | Removed logo | 7/12/21 | CG |
| N/A | B | Update to new format | 6/14/17 | RE |
| N/A | A | Actuator Update | 9/07/06 | CLS |

| | | | | | | | |
|----------|-----|-------|---------|----------|----------|------|---|
| DWN. BY | CLS | DATE | 9/07/06 | DWG. NO. | SRCD414M | REV. | C |
| CHK'D BY | RE | SCALE | NTS | | | | |