



———— Factory Piping
 - - - - Field Piping By Others

SRCD 417M

(CDS) ATU\CONTROL DIAGRAMS\PNEUMATIC\

Control Wiring Diagram

RANO 3 - 8 PSI Pneumatic
 Pressure Independent

Unless Otherwise Specified:
 1. Dimensions Are In Inches.
 2. Tolerances Are:
 Fractions Decimals Angles
 $\pm 1/32$ $\pm .X = .1$ $\pm 1^\circ$
 $\pm .XX = .02$
 $\pm .XXX = .010$

ECN. No.	Rev	Description	Date	Rev'd By:
N/A	C	Removed logo	7/12/21	CG
N/A	B	Update to new format	6/14/17	RE
N/A	A	Actuator Update	9/07/06	CLS

DWN. BY	CLS	DATE	9/07/06	DWG. NO.	SRCD417M	REV.	C
CHK'D BY	RE	SCALE	NTS				