






Transformer Options:  
 152N - No Xformer  
 152A - 120 / 24  
 152C - 277 / 24  
 152F - 240 / 24

SHIP WITH  
 DAMPER  
 OPEN



—— Factory Piping  
 - - - Field Piping By Others

Actuator-ML6161B-2024, 90 Second  
 Thermostat-RDG400 24 V Digital

THCD 152  
 (CDS) ATU\CONTROL DIAGRAMS\ELECTRIC\

# Control Wiring Diagram

Single Duct Air Terminal  
 Cooling Only VAV

Phone: 715.359.6171  
 Fax: 715.355.2399  
 Parts : 800.355.5354  
 gfcinfo@greenheck.com  
 www.greenheck.com

ECN. No.	Rev	Description	Date	Rev'd By:
N/A	J	Removed logo	7/7/21	CG
N/A	I	RED COMMON WIRE MOVED TO GO	11/02/17	RML
N/A	H	UPDATED TO NEW FORMAT	08/22/17	RML
N/A	G	Revised Digital Thermostat	12/12/16	DSG

Unless Otherwise Specified: 1. Dimensions Are In Inches. 2. Tolerances Are: Fractions Decimals Angles $\pm 1/32$ $\pm .X = .1$ $\pm 1^\circ$ $\pm .XX = .02$ $\pm .XXX = .010$			<b>Control Wiring Diagram</b>		
DWN. BY DB		DATE 9/12/02			
CHK'D BY DSG		SCALE NTS		DWG. NO.	REV.
				THCD152	J