



——— Factory Piping  
 - - - Field Piping By Others

**THCD 117M**

(CDS) ATU\CONTROL DIAGRAMS\PNEUMATIC\

# Control Wiring Diagram

RANO 3 - 8 PSI Pneumatic  
Pressure Independent

Unless Otherwise Specified:  
 1. Dimensions Are In Inches.  
 2. Tolerances Are:  
 Fractions Decimals Angles  
 $\pm 1/32$   $\pm .X = .1$   $\pm 1^\circ$   
 $\pm .XX = .02$   
 $\pm .XXX = .010$

ECN. No.	Rev	Description	Date	Rev'd By:
N/A	C	Removed logo	7/7/21	CG
N/A	B	Update to new format	6/13/17	RE
N/A	A	Actuator Update	9/07/06	CLS

DWN. BY	CLS	DATE	9/07/06	DWG. NO.	THCD 117M	REV.	C
CHK'D BY	RE	SCALE	NTS				