




Model: XG-AFL-FH 1 Slot - Offset Height Frame - Surface Mounted


XG-AFL-FH - Surface Mounted




Standard Blade



Combo Blade



Open End



End Cap

XG-AFL-FH - 1 Slot						
Model	Unit Face	F Face	Height	Height	Slot	Neck
	A	B	H1	H2	S	W1
XG-AFL-FH-10	3 1/4	1 1/8	1 15/16	2 9/16	1	3 1/4
XG-AFL-FH-15	3 3/4	1 1/8	1 15/16	2 9/16	1 1/2	3 3/4
XG-AFL-FH-20	4 1/4	1 1/8	1 15/16	2 9/16	2	4 1/4
XG-AFL-FH-25	5 3/4	1 5/8	1 15/16	2 9/16	2 1/2	5 3/4
XG-AFL-FH-30	6 1/4	1 5/8	1 15/16	2 9/16	3	6 1/4

1. Available Finishes

Standard Finish:

20 - White Face and Black Interior

Optional Finish

02 - Satin Silver Face and Black Interior

03 - Black Face and Black Interior

28 - Custom Face Color and Black Interior

2. Available Accessories

3. Available Options

1EC - (1) End Cap
2EC - (2) End Cap
OO - Open / Open

4. Construction Details

- Material Extruded Aluminum
- C - Combo Pattern Controller
- S - Standard Pattern Controller
- Standard Single Section Size: (12" minimum - 96" maximum)
- Lengths larger than 96" made in multiple sections

All Dimensions ±1/16"