



	1	2	3	4	5	6	7	8
A								
B								
C								
D								
E						Notes:		
						Performed by:		
	P 5.709	AB 5.520	J 1.835	2E 4.236	A 6.142	Checked:		
	H 0.343	G 0.075	HB 1.559	HK 2.650	FC 6.299	Customer:		
	2F 2.748	B 3.543	C 9.492	BA 2.500	N-W 1.500	Single Phase: W01 (Rolled Steel) - ODP - Premium Efficiency (DOE)		
F	ES 1.260	d1 A 3,15	U 0.500	AA NPT 1/2"	R 0.451			
	LL 3.835	LM 3.697	BB 0.524	D 3.000	XO 0.524	Single-phase induction motor Frame 48 - ODP		20-JUN-2016
	HD2 7.165	O 5.830	HC2 4.165					
								