




For 60Hz use on PWM, VT 1000:1, CT 3:1, 1.0SF

Inverter Duty Motor

MODEL 030180T3E286T-W40
MADE IN BRAZIL
14448032

PH 3		FR 284/6T		HP(kW) 30.0(22.0)		Hz 60					
V 230/460		A 69.8/34.9		RPM 1770		DES B		<div> → 6311-Z-C3 → 6211-Z-C3</div> <div>MOBIL POLYREX EM 18 g 20000 h</div>			
NEMA NOM EFF		94.1 %		INS. CL. F ΔT 80 K		IP23					
ENCL ODP		DUTY		CONT.		AMB. 40°C					
CODE G		PF 0.84		SF 1.25		SFA 87.3/43.6					
USABLE @208V 77.2 A SF 1.15 SFA 88.8								ALT 1000 m.a.s.l. 397 Lbs			
18.5kW 50Hz 380V 35.7A 1470RPM SF1.00 EFF 92.6% (IE3)											