



HIGH VOLTAGE CAPACITOR START
NO OVERLOAD SELECT ROTATION



FOR C.W. ROTATION
INCHANGE RED (T8)
AND BLACK (T5)

				TOLERANCES UNLESS SPECIFIED	 Regal Beloit America, Inc.		DRAWN PGK 08-26-1996
				DEC.	INCHES		CHK ML 09-09-1996
				.X	±.1		APPD GK 09-09-1996
03	UPDATED LINE LEADS AS PER ECO-0133427	UD	10/23/17	GSR .XX	±.02	TITLE CONNECTION DIAGRAM	SCALE 1=1
02	LEAD T4 CHANGED TO T3 PER ECO-0112860	AS	11/10/16	MSD .XXX	±.005		REF 102006-57
01	REDRAWN ON CADD	PGK	09-09-1996	.XXXX	±.0005	MAT'L.	FMF
NO.	REVISION	BY & DATE		CHK ANG	±7'30"	FINISH	PREV
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT							CAD FILE A-102006-57
				RFP	SIZE A	DRAWING NO. A-102006-57	REV. 03
				DIST		PAGE OF	