



Product Features:

- Available with 1/2" wide frames
- Available with 7/32" or 1/8" thick bars
- Pencil proof 17/64" bars available
- Available with 1/2" or 1/4" bar spacing
- Available for straight and curved applications
- Various frame types are available for different applications
 - H - Concealed Mounting Hanger
- Available in lengths up to 1200 in multiple sections
- Model LBG is available in widths from 1 1/2" to 24"
- Can come with hanger brackets for concealed mounting
- Available with sub-frames for specific applications
- Extruded aluminum construction


Finishes




CFD Throw Pattern Visualization




Optional Accessories:

















End View






Side View












End Border / End Border	
Length	L = 1/2













Open / Open	
Length	L = 0















End Border / Open	
Length	L = 1/4


























































End Border / End Border	
Length	L = 1/2



Open / Open	
Length	L = 0



End Border / Open	
Length	L = 1/4

