

Model DS

Destratification Fan

Introducing model DS high volume, low speed (HVLS) fans by Greenheck. Designed from the ground-up (or ceiling-down) by Greenheck's experienced engineers, model DS provides year-round comfort and improved building efficiency in any application.

Massive Air Movement

With performance up to 243,000 cfm, one Greenheck DS fan can replace up to 40 pedestal circulators!

Plug-and-Play, Not All-Day

Say goodbye to all-day HVLS fan installation. Featuring a universal ceiling mount and unique plug-and-play wiring, the DS fan can be installed in less than half the time of a traditional HVLS fan.

No Gearbox, No Problems

With its unique direct drive motor, model DS is up to 20% more efficient than gearbox-driven fans. Plus it's lighter and up to 10 dBA quieter too.

Third-Party Certification


As the industry's only AMCA certified HVLS fan, model DS ensures that you get the right amount of airflow for your facility.

Make It Pop

Your building makes a statement so your fans should too. Choose from standard color schemes or personalize your fan with optional finish colors.

Peace Of Mind

With over 70 years of experience in the HVAC industry, Greenheck knows how to build value in air. Every DS fan is manufactured with the highest standards of safety and quality to ensure that you're getting the best HVLS fan on the market.



Certified data may be found in Greenheck's Computer Aided Product Selection Program (CAPS).