

INDUSTRY LEADING HVLS FANS

MODEL DS

Innovation applied.

 **GREENHECK**
Building Value in Air.



Simplified product selection.

Take the guesswork out of HVLS fan specification. Greenheck's easy to use eCAPS® selection software ensures that you get the right amount of airflow for your facility.

Lower operating costs. Greenheck's unique airfoil blade design maximizes fan efficiency and performance.

Direct drive motors with preprogrammed VFDs also make DS fans up to 20% more efficient than competitor products.

Easy, quick installation.

Factory-wired for plug-and-play convenience, the DS can be installed in less than half the time of a traditional HVLS fan.

Industry leading performance.

As the first AMCA certified HVLS fan for Circulating Fan Performance, depend on model DS to deliver up to 243,000 cfm — more air than the competition.



MODEL DS

■ **Safe, simple operation.**

Intuitive controls, intelligent VFDs and more than 10 standard safety features. Worry-free, reliable operation.

■ **Personalize your fan.**

Choose from 22 decorative and protective finishes or customize your fan with unlimited color match.

High Volume, Low Speed Fans

Greenheck, the world's leading manufacturer of air movement, control and conditioning equipment, now offers the best performing HVLS ceiling fans on the market. Model DS is the industry's first destratification fan that's AMCA certified for Circulating Fan Performance. It eliminates thermal stratification that occurs in buildings during cold months and provides a comfortable cooling breeze when it's warm outside. In either application, the DS reduces load on your HVAC system resulting in lower energy costs and increased occupant comfort. This makes model DS an ideal solution for any commercial or industrial setting.

Don't Just Take Our Word for It...

Check out the DS fan for yourself! Use our popular eCAPS product selection software to size and configure the right DS fans for your building today!



It looks great, too.

Model DS is available in two standard, preconfigured color schemes that give your facility a little style without distracting from the interior design. With anodized airfoil blades and either blue or black accents, both options offer a timeless look that is sure to please.


Want something that's a little bolder? DS fans can also be personalized to brighten up restaurants, field houses, brew pubs and other public spaces where people gather. Fans can be painted in any color, anodized or finished with a unique woodgrain texture to match your facility's décor.

Need a finish that's more functional than aesthetic? Choose from a variety of vibrant safety colors to alert employees and forklift drivers of the fan's location in warehouses, distribution centers, and manufacturing facilities.

Whatever finish your choose, model DS is sure to fit your building's style and needs!



Standard Anodized and Blue. A clear anodize finish on the airfoil blades with Greenheck's classic blue paint on the fan hub and winglets.



Standard Anodized and Black. A clear anodize finish on the airfoil blades with a flat black paint on the fan hub and winglets.



P.O. Box 410 | Schofield, WI 54476-0410 USA
Phone 715.359.6171 | Fax 715.355.2399 | greenheck.com

HVLS DS | November 2018 | Copyright © 2018 Greenheck Fan Corp.

Bright, exciting colors and finishes.*

Safety Orange

Safety Yellow

Signal Violet

Utility Red

Greenheck Blue

Equipment Green

Bone White

Ivory

Telegray 4

Concrete Gray

Hampton Brown

Medium Bronze

Flat Black

Cinnamon Cherry

Dark Oak

Golden Knotty Pine

Honey Knotty Pine

Natural Cherry

**Color is for reference only and is not to be used for final color matching.*