


Standard Construction Features

MODEL DS

Innovation applied.



- **Airfoils** - Unique CFD-optimized aluminum airfoil design, airfoils are available in 8 to 24 foot diameter fans.
- **Winglets** - Choose from two standard color schemes, Greenheck blue or flat black.
- **Intelligent VFD & Motor** - Factory-mounted, wired & programmed drive. Direct drive motor and drive combination result in high efficiency, low sound and ultra light installation. Smart features include overspeed and impact detection along with temperature, voltage and current monitoring. Motor maximum ambient temperature is 104°F.
- **Controller** - Keypad control with LCD display can operate up to five fans. Includes 50 feet of CAT-5e Control Cable.
- **Fire Relay** - Low voltage relay can be wired into a building's fire suppression system for automatic fan shutdown when sprinklers are activated.
- **Ceiling Mount & Downtube** - 3½-foot downtube with universal ceiling mount and self-leveling joint.
- **Logo Plate** - Greenheck logo represents on two standard plate color schemes, Greenheck blue or flat black. Hub retention bracket included for added safety.
- **Guy Wire Kit** - Safely secures using four 15-foot guy wires with end clips, clamps, and high quality Gripple® turnbuckles.
- **Power Cable** - 3-foot factory-wired power cable with plug.
- **10-year Warranty** - Factory tested for years of reliable operation and includes 10-year warranty.
- **Certifications** - First AMCA certified HVLS fan for Circulating Fan Performance. Fans are UL/cUL Listed Standard 507.



Certified data may be found in Greenheck's Computer Aided Product Selection Program (CAPS).

 **GREENHECK**
Building Value in Air.

MODEL DS

Innovation applied.




LED Light

- 150W Equivalent, 19,500 Lumen


NEMA-3R Disconnect Switches

- Toggle
- Heavy Duty
- Fused Protection




Extended Warranty

- 11 Years
- 12 Years
- 13 Years
- 14 Years



Extended Length Control Wire

- 75 Feet
- 100 Feet



Extended Drop Lengths


- 4 to 10 Feet



Optional Accessories

Mounting Hardware Kits

- I-Beam
- Steel Truss
- Unistrut®
- Wood Beam
- Z-Purlin



Custom Finish Colors

- 22 Standard Colors
- Anodize
- Hi-Pro Polyester
- Kynar
- Wood Grain



Extended Length Power Cable

- 10 Feet
- With or Without Prewired Plug

