

All louvers shown meet some or all Florida and International Building Code Requirements for the hurricane-prone region.

Model Name Max. Wind-load	Construction Description Dimensions – inches (mm)	AMCA Certifications	AMCA Listed	Miami-Dade County, FL NOA No.	Florida Product Approved No.	Florida Test Protocols	Minimum Opening	Maximum Section	Maximum Opening
							Dimensions – inches (mm)		
Miami-Dade Approved Louvers and Penthouses									
K6746MD* 150 PSF	6 in. (152) deep, extruded aluminum horizontal drainable blade louver	Water, Air	AMCA 550 (with factory attached VCD-40 damper in closed position), AMCA 540 Basic Level D and Enhanced Level E (with 0.125 blade/frame)	22-0816.11 EXP. 12/6/23	FL10093	TAS 201, TAS 202, TAS 203 TAS-100(A): SCV501MD, SCV660MD (with VCD-40 damper blades closed)	12 W x 12 H (305 W x 305 H)	72 W x 144 H (1829 W x 3658 H)	Unlimited W x 144 H (Unlimited W x 3658 H)
K6746MDE 150 PSF	6 in. (152) deep, extruded aluminum horizontal drainable blade louver		AMCA 550 (with factory attached VCD-40 damper in closed position), AMCA 540 Basic Level D	20-0929.09 EXP. 2/4/26	FL19676		12 W x 12 H (305 W x 305 H)	48 W x 48 H (1219 W x 1219 H)	48 W x 48 H (1219 W x 1219 H)
K8206AMD 110 PSF	6 in. (152) deep, extruded aluminum adjustable horizontal drainable blade louver		AMCA 550 (with damper in closed position), AMCA 540 Basic Level D	21-0526.13 EXP. 12/5/23	FL16743		12 W x 16 H (305 W x 406 H)	60 W x 120 H (1524 W x 3048 H)	Unlimited W x 120 H (Unlimited W x 3048 H)
SCC901MD 130 PSF	9 in. (229) deep, extruded aluminum horizontal front and vertical rear rain resistant blades	AMCA 550, AMCA 540 Enhanced Level E	21-0526.11 EXP. 7/28/26	FL19685	12 W x 12 H (305 W x 305 H)		60 W x 120 H (1524 W x 3048 H)	Unlimited W x 120 H (Unlimited W x 3048 H)	
SCH601MD* 150 PSF	6 in. (152) deep, extruded aluminum horizontal rain resistant blade louver	AMCA 550 (with factory attached VCD-40 damper in closed position), AMCA 540 Enhanced Level E	22-0816.12 EXP. 11/1/23	FL10093	12 W x 7 H (305 W x 178 H)		72 W x 144 H (1829 W x 3658 H)	Unlimited W x 144 H (Unlimited W x 3658 H)	
SCH601MDE 150 PSF	6 in. (152) deep, extruded aluminum horizontal rain resistant blade louver	AMCA 540 Enhanced Level E	20-0929.08 EXP. 12/24/25	FL19673	12 W x 7 H (305 W x 178 H)		48 W x 48 H (1219 W x 1219 H)	48 W x 48 H (1219 W x 1219 H)	
SCC550MD 100 PSF	5.5 in. (140) deep, extruded aluminum horizontal front and vertical rear rain resistant blades	Water, Air and Wind Driven Rain	AMCA 550, AMCA 540 Enhanced Level E	21-0917.11 EXP. 8/15/24	FL30298		12 W x 12 H (305 W x 305 H)	60 W x 96 H (1524 W x 2438 H)	Unlimited W x 96 H (Unlimited W x 2438 H)
SCV302MD 100 PSF	3 in. (76) deep, extruded aluminum vertical rain resistant blade louver		AMCA 550, AMCA 540 Basic Level D	21-0917.13 EXP. 6/6/24	FL29695		12 W x 12 H (305 W x 305 H)	60 W x 96 H (1524 W x 2438 H)	Unlimited W x 96 H (Unlimited W x 2438 H)
SCV501MD 130 PSF	5 in. (127) deep, extruded aluminum vertical rain resistant blade louver		AMCA 550, AMCA 540 Enhanced Level E	21-0526.15 EXP. 8/6/25	FL19278		12 W x 12 H (305 W x 305 H)	120 W x 120 H, Limited to 70 ft ² (3048 W x 3048 H, Limited to 6.5 m ²)	Unlimited W x 120 H (Unlimited W x 3048 H)
SCV660MD 150 PSF	6 in. (152) deep, extruded aluminum vertical rain resistant blade louver		AMCA 550, AMCA 540 Enhanced Level E	22-0707.09 EXP. 10/4/27	FL16746		12 W x 12 H (305 W x 305 H)	48 W x 120 H or 60 W x 96 H (1219 W x 3048 H or 1524 W x 2438 H or 2438 W x 1524 H)	Unlimited W x 120 H (Unlimited W x 3048 H)
SCH601PD 115 PSF	6 in. (152) deep, extruded aluminum horizontal rain resistant blade louvered penthouse	Not Applicable	Not Applicable	18-0314.03 EXP. 6/19/23	FL11357	Min. Throat W x L x Min. H 12 x 12 x 12 (305 x 305 x 305)	Max. Throat W x L x Max. H 84 x 108 x 84 (2134 x 2743 x 2134)	Max. Throat W x L x Max. H 84 x 108 x 84 (2134 x 2743 x 2134)	
K6746PD 115 PSF	6 in. (152) deep, extruded aluminum horizontal drainable blade louvered penthouse			18-0314.04 EXP. 6/19/23	FL11357	Min. Throat W x L x Min. H 12 x 12 x 12 (305 x 305 x 305)	Max. Throat W x L x Max. H 84 x 108 x 84 (2134 x 2743 x 2134)	Max. Throat W x L x Max. H 84 x 108 x 84 (2134 x 2743 x 2134)	
Florida Product Approved Louvers									
K6744X* Max. 200 PSF [^]	4 in. (102) deep, extruded aluminum horizontal drainable blade louver	Water, Air	AMCA 540 Basic Level D	Not Applicable	FL7708, FL35290	Standard: TAS 202	12 W x 9 H (305 W x 229 H)	120 W x 144 H Limited to 70 ft ² (3049 W x 3658 H Limited to 6.5 m ²)	Unlimited W x 144 H or 120 W x Unlimited H (Unlimited W x 3658 H or 3048 W x Unlimited H)
K6746X* Max. 200 PSF [^]	6 in. (152) deep, extruded aluminum horizontal drainable blade louver		AMCA 540 Enhanced Level E		FL7708, FL35290		Welded: TAS 201, TAS 202, TAS 203		
SCH501X* Max. 200 PSF [^]	5 in. (127) deep, extruded aluminum horizontal rain resistant blade louver	AMCA 540 Enhanced Level E	FL7708, FL35290		12 W x 7 H (305 W x 178 H)				

*Also available in architectural shapes. ^Size/section dependent.