









Model: XG-7500-1 Perforated Hinged Face with Face Mounted Pattern Controller - Flush Surface Mount

XG-7500-1 - Flush Surface Mount



Listed Size
Nominal
Face
24 x 24
12 x 12

Air Pattern Options					Fixed 360° Radial Round Air Controller
1 Way	2 Way Corner	2 Way	3 Way	4 Way	
					


1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Finish 02 Satin Silver 03 Black 22 BBP - Black Backpan - White Face Optional Finish 28 Custom Color	XG-BDS - Butterfly Damper XG-RDS - Steel Radial Shutter Damper XG-TBPF - T-Bar Plaster Frame XG-G3 - Equalizing Grid (Round)	AF - Aluminum Face DF - Drop Face AL - Aluminum Face and Backpan	<ul style="list-style-type: none"> Steel Construction (Standard) Sizes Available only as listed Neck sizes available: 6, 8, 10, 12, 14 & 16 Face is Hinged

All Dimensions $\pm 1/16"$


Model: XG-7500-6

Perforated Hinged Face with Face Mounted Pattern Controller - Lay In T-Bar

XG-7500-6 - Lay in T-Bar









Side View



Face View

Listed Size
Nominal
Face
24 x 24
12 x 12

Air Pattern Options					Fixed 360° Radial Round Air Controller
1 Way	2 Way Corner	2 Way	3 Way	4 Way	
					


1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Finish 02 Satin Silver 03 Black 22 BBP - Black Backpan - White Face Optional Finish 28 Custom Color	XG-BDS - Butterfly Damper XG-RDS - Steel Radial Shutter Damper XG-TBPF - T-Bar Plaster Frame XG-G3 - Equalizing Grid (Round) XG-EQ = Earthquake Straps	AF - Aluminum Face DF - Drop Face AL - Aluminum Face and Backpan	<ul style="list-style-type: none"> ● Steel Construction (Standard) ● Sizes Available only as listed ● Neck sizes available: 6, 8, 10, 12, 14 & 16 ● Face is Hinged

All Dimensions $\pm 1/16"$


Model: XG-7500-8

Perforated Hinged Face with Face Mounted Pattern Controller - Tegular T-Bar

XG-7500-8 - Tegular T-Bar



Side View



Face View

Listed Size
Nominal
Face
24 x 24
12 x 12

Air Pattern Options					Fixed 360° Radial Round Air Controller
1 Way	2 Way Corner	2 Way	3 Way	4 Way	


1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Finish 02 Satin Silver 03 Black 22 BBP - Black Backpan - White Face Optional Finish 28 Custom Color	XG-BDS - Butterfly Damper XG-RDS - Steel Radial Shutter Damper XG-G3 - Equalizing Grid (Round)	AF - Aluminum Face DF - Drop Face AL - Aluminum Face and Backpan	<ul style="list-style-type: none"> Steel Construction (Standard) Sizes Available only as listed Neck sizes available: 6, 8, 10, 12, 14 & 16 Face is Hinged

All Dimensions $\pm 1/16"$


Model: XG-7500-9

Perforated Hinged Face with Face Mounted Pattern Controller - Bolt Slot/Donn Finline

XG-7500-9 - Bolt Slot




Side View



Face View

Listed Size
Nominal
Face
24 x 24
12 x 12



1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Finish 02 Satin Silver 03 Black 22 BBP - Black Backpan - White Face Optional Finish 28 Custom Color	XG-BDS - Butterfly Damper XG-RDS - Steel Radial Shutter Damper XG-G3 - Equalizing Grid (Round) XG-EQ - Earthquake Straps	DF - Drop Face	<ul style="list-style-type: none"> Steel Construction (Standard) Sizes Available only as listed Neck sizes available: 6, 8, 10, 12, 14 & 16 Face is Hinged

All Dimensions ±1/16"