





Sidewall Supply Grilles and Registers
Steel - Double Deflection

- Models: **XG-V4004S-1** Double Deflection Grille - Vertical Front Blades
XG-H4004S-1 Double Deflection Grille - Horizontal Front Blades
XG-V4004S-1 XG-OBD Double Deflection Grille - Vertical Front Blades - with Opposed Blade Damper
XG-H4004S-1 XG-OBD Double Deflection Grille - Horizontal Front Blades - with Opposed Blade Damper


Model: XG-V4004S-1 (Double Deflection Grille - Vertical Front Blades) Front View (Double Deflection) (Vertical Front Blades)




Model: XG-H4004S-1 (Double Deflection Grille - Horizontal Front Blades) Front View (Double Deflection) (Horizontal Front Blades)



Option: XG-V4004S-1 XG-OBD (Double Deflection Register) (Vertical Front Blades) With Opposed Blade Damper



Option: XG-H4004S-1 XG-OBD (Double Deflection Register) (Horizontal Front Blades) With Opposed Blade Damper




Notes: (check if provided)

1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White. Optional Finish (extra charge): 02 Satin Silver 03 Black. 28 Custom Color / Setup Charge	XG-OBD - Steel Opposed Blade Damper. XG-OBDA - Aluminum Opposed Blade Damper. XG-L9 - Equalizing Grid. XG-PF - Plaster Frame. XG-LIPF - Lay-In Plaster Frame XG-TR - Transition Square / Rectangular to Round up to 22x22 XG-TR - Deep Transition Used with Dampers IS - Insect Screen	NSH - No Screw Holes	<ul style="list-style-type: none"> Steel Construction. Oversized units made in multiple sections, each with full flanges. Mullion strips provided for joining units in field.


Ceiling Supply Grilles and Registers
Steel - Double Deflection

Models: **XG-H4004S-6** Double Deflection Grille - Horizontal Front Blades - T-Bar Lay-In - With Filter Panel
XG-V4004S-6 Double Deflection Grille - Vertical Front Blades - T-Bar Lay-In - With Filter Panel

Model: XG-H4004S-6 (Double Deflection Grille) Lay in T-Bar - With Filler Panel (Horizontal Front Blades)



Model: XG-V4004S-6 (Double Deflection Grille) Lay in T-Bar - With Filler Panel (Vertical Front Blades)



Notes: (check if provided)

1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White. Optional Finish (extra charge): 02 Aluminum 03 Black	XG-OBD - Steel Opposed Blade Damper. XG-OBDA - Aluminum Opposed Blade Damper. XG-L9 - Equalizing Grid. XG-PF - Plaster Frame.		<ul style="list-style-type: none"> Steel Construction. Oversized units made in multiple sections, each with full flanges. Mullion strips provided for joining units in field.