



Model: XG-RPF-1 Hinged Core Perforated Face - Flush Surface Mount
XG-RPF-6 Hinged Core Perforated Face - T-Bar Lay-In


XG-RPF-1 - Flush Surface Mount




Face View



XG-RPF-6 - T-Bar Lay-In



Face View




Filter Depth	H
1"	2 7/16"
2"	3 7/16"

Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.


1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Finish 24 Mill Finish Optional Finish 02 Satin Silver 03 Black 28 Custom Color	OBD - Steel Opposed Blade Damper OBDA - Aluminum OBD L9 - Equalizing Grid PF - Plaster Frame TBPF - T-Bar Plaster Frame TR - Square to Round Transition TR-Deep - Deep Transition LIPF - Lay-In Plaster Frame	IS - Insect Screen 1"FF - 1" Filter Frame 2"FF - 2" Filter Frame	<ul style="list-style-type: none"> Frame and Perforated Face are Aluminum. Can be ordered to fit standard T-Bar module panels. Filter Size: Listed size - 1/8" Odd/Fractional Sizes Available
All Dimensions ±1/16"			

Model: XG-RPF-RC-1 Removable Core Perforated Face - Flush Surface Mount
XG-RPF-RC-6 Removable Core Perforated Face - T-Bar Lay In


XG-RPF-RC-1 - Flush Surface Mount




Face View



XG-RPF-RC-6 - T-Bar Lay In



Face View



Filter Depth	H
1"	2 7/16"
2"	3 7/16"

Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.

1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Finish 24 Mill Finish Optional Finish 02 Satin Silver 03 Black 28 Custom Color	OBD - Steel Opposed Blade Damper OBDA - Aluminum OBD L9 - Equalizing Grid PF - Plaster Frame TBPF - T-Bar Plaster Frame TR - Square to Round Transition TR-Deep - Deep Transition LIPF - Lay-In Plaster Frame	IS - Insect Screen 1"FF - 1" Filter Frame 2"FF - 2" Filter Frame	<ul style="list-style-type: none"> Frame and Perforated Face are Aluminum. Can be ordered to fit standard T-Bar module panels. Filter Size: Listed size - 1/8" Odd/Fractional Sizes Available
All Dimensions ±1/16"			