





Model: XG-2200F      7/32 Bars on 1/2" Spacing - 0°, 15° and 30° Blades


**XG-2200F - Floor Frame**




0° Deflection



15° Deflection




30° Deflection




1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Optional Finish No Extra Charge 24 Mill Finish Optional Finish (extra charge) 02 Satin Silver 03 Black 04 Clear Anodized 28 Special/Setup Charge			<ul style="list-style-type: none"> <li>• Widths available in 1/2" increments from 1 1/2" to 8" for Series 2200F.</li> <li>• Lengths available in single pieces up to 72".</li> <li>• Longer sections are available only as separate non-connected sections.</li> <li>• For Lengths less than 72" round up to next Listed size.</li> </ul> <p style="text-align: right;">All Dimensions <math>\pm 1/16"</math></p>

Model: XG-2200FP      17/64" Bars on 1/2" Spacing - 0°, 15° and 30° Blades - Pencil Proof


### XG-2200FP - Floor Frame Pencil Proof



End View




Side View




Face View


0° Deflection



15° Deflection




30° Deflection



1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Optional Finish No Extra Charge 24 Mill Finish Optional Finish (extra charge) 02 Satin Silver 03 Black 04 Clear Anodized 28 Special/Setup Charge			<ul style="list-style-type: none"> <li>• Widths available in 1/2" increments from 1 1/2" to 8" for Series 2200F.</li> <li>• Lengths available in single pieces up to 72".</li> <li>• Longer sections are available only as separate non-connected sections.</li> <li>• For Lengths less than 72" round up to next Listed size.</li> </ul> <p style="text-align: right;">All Dimensions <math>\pm 1/16"</math></p>

Model: XG-2200H      7/32" Bars on 1/2" Centers - 0°, 15° and 30° Blades

### XG-2200H - Ceiling or Wall Mount



1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Optional Finish No Extra Charge 24 Mill Finish Optional Finish (extra charge) 02 Satin Silver 03 Black 04 Clear Anodized 28 Special/Setup Charge			<ul style="list-style-type: none"> <li>• Widths available in 1/2" increments from 1 1/2" to 24" for Series 2200H.</li> <li>• Lengths available in single pieces up to 72".</li> <li>• Longer sections are available only as separate non-connected sections.</li> <li>• Core welded in Place</li> </ul> <p style="text-align: right;">All Dimensions ±1/16"</p>