


Model: XG-6600SQ-6 Supply - Non Insulated - T-Bar lay In

XG-6600SQ-6 - T-Bar Lay-In



Model	Dim. W	1 Slot	2 Slot	3 Slot	4 Slot
		Dim. A	Dim. A	Dim. A	Dim. A
6650SQ	1/2	2 3/4	4	5 1/4	6 1/2
6675SQ	3/4	3	4 1/2	6	7 1/2
6610SQ	1	3 1/4	5	6 3/4	8 1/2


Round Neck Diameter
6
8
10
12

1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 20 - White Face, Black Back 21 - Clear anodized with Black Pattern Controller 03 - Black Optional Finish: 28 - Special/Setup Charge	XG-D3 - Radial Opposed Blade Damper XG-BDS - Butterfly Damper XG-RSD - Steel Radial Shutter Damper XG-EQ - Equalizing Grid XG-TBPF - T-Bar Plaster Frame		<ul style="list-style-type: none"> Only Available in 24 x 24 Sizes available in only 1-8 slots

All Dimensions ±1/16"

Model: XG-6600SQ-8 Supply - Non Insulated - Tegular T-Bar

XG-6600SQ-8 - Tegular T-Bar




Model	Dim. W	1 Slot	2 Slot	3 Slot	4 Slot
		Dim. A	Dim. A	Dim. A	Dim. A
6650SQ	1/2	2 3/4	4	5 1/4	6 1/2
6675SQ	3/4	3	4 1/2	6	7 1/2
6610SQ	1	3 1/4	5	6 3/4	8 1/2

1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 20 - White Face, Black Back 21 - Clear anodized with Black Pattern Controller 03 - Black Optional Finish: 28 - Special/Setup Charge	XG-D3 - Radial Opposed Blade Damper XG-BDS - Butterfly Damper XG-RSD - Steel Radial Shutter Damper XG-EQ - Equalizing Grid XG-TBPF - T-Bar Plaster Frame		<ul style="list-style-type: none"> Only Available in 24 x 24 Sizes available in only 1-8 slots

All Dimensions ±1/16"

Model: XG-6600SQ-9 Supply - Non Insulated - Bolt Slot / Donn Ceiling Grid

XG-6600SQ-9 - Bolt Slot / Donn Finline Ceiling Grid



Model	Dim. W	1 Slot	2 Slot	3 Slot	4 Slot
		Dim. A	Dim. A	Dim. A	Dim. A
6650SQ	1/2	2 3/4	4	5 1/4	6 1/2
6675SQ	3/4	3	4 1/2	6	7 1/2
6610SQ	1	3 1/4	5	6 3/4	8 1/2

1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 20 - White Face, Black Back 21 - Clear anodized with Black Pattern Controller 03 - Black Optional Finish: 28 - Special/Setup Charge	XG-D3 - Radial Opposed Blade Damper XG-BDS - Butterfly Damper XG-RSD - Steel Radial Shutter Damper XG-EQ - Equalizing Grid XG-TBPF - T-Bar Plaster Frame		<ul style="list-style-type: none"> • Only Available in 24 x 24 • Sizes available in only 1-8 slots

All Dimensions ±1/16"