




Model: XG-9000S-1

Louvered Face - Modular Core - Flush Surface Mount


XG-9000S-1 - Flush Surface Mount




Front View




1 - Way




2 - Way
Corner



2 - Way
Opposite



3 - Way



4 - Way

1. Available Finishes

- Standard Finish:
- 01 White
- Finish
- 24 Mill Finish
- Optional Finish
- 02 Satin Silver
- 03 Black
- 28 Custom Color

2. Available Accessories

- XG-OBDA - Steel Opposed Blade Damper
- XG-OBDA - Aluminum OBD
- XG-L9 - Equalizing Grid (Sq / Rect)
- XG-TR - Transition Square to Round
- XG-TR - Deep Transition
- XG-PF - Plaster Frame
- XG-TBPF - T-Bar Plaster Frame
- XG-LIPF - Lay-In Plaster Frame

3. Available Options

4. Construction Details


- Available Sizes Only as Listed
- Steel Frame and Cores
- Units Available with Multiple Cores depending on Neck Size

All Dimensions ±1/16"


Model: XG-9000S-2

Louvered Face - Modular Core - Beveled Surface Mount


XG-9000S-2 - Beveled Surface Mount




Side View




Front View




1 - Way




2 - Way
Corner



2 - Way
Opposite



3 - Way



4 - Way

1. Available Finishes

- Standard Finish:
- 01 White
- Finish
- 24 Mill Finish
- Optional Finish
- 02 Satin Silver
- 03 Black
- 28 Custom Color

2. Available Accessories

- XG-OBDA - Steel Opposed Blade Damper
- XG-OBDA - Aluminum OBD
- XG-L9 - Equalizing Grid (Sq / Rect)
- XG-TR - Transition Square to Round
- XG-TR - Deep Transition
- XG-PF - Plaster Frame
- XG-TBPF - T-Bar Plaster Frame
- XG-LIPF - Lay-In Plaster Frame

3. Available Options


4. Construction Details

- Available Sizes Only as Listed
- Steel Frame and Cores
- Units Available with Multiple Cores depending on Neck Size


All Dimensions $\pm 1/16"$

Model: XG-9000S-6 Louvered Face - Modular Core - Lay In T-Bar

XG-9000S-6 - Lay In T-Bar




Side View



Available Module Size
12 x 12
24 x 24

Front View




1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Finish 24 Mill Finish Optional Finish 02 Satin Silver 03 Black 28 Custom Color	XG-OBDA - Steel Opposed Blade Damper XG-OBDA - Aluminum OBD XG-L9 - Equalizing Grid (Sq / Rect) XG-TR - Transition Square to Round XG-TR - Deep Transition XG-PF - Plaster Frame XG-TBPF - T-Bar Plaster Frame XG-LIPF - Lay-In Plaster Frame		<ul style="list-style-type: none"> Available Sizes Only as Listed Steel Frame and Cores Units Available with Multiple Cores depending on Neck Size


All Dimensions ±1/16"

Model: XG-9000S-8 Louvered Face - Modular Core - Tegular T-Bar

XG-9000S-8 - Tegular T-Bar




Side View



Available Module Size
24 x 24

Front View




1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Finish 24 Mill Finish Optional Finish 02 Satin Silver 03 Black 28 Custom Color	XG-OBD - Steel Opposed Blade Damper XG-OBDA - Aluminum OBD XG-L9 - Equalizing Grid (Sq / Rect) XG-TR - Transition Square to Round XG-TR - Deep Transition XG-PF - Plaster Frame XG-TBPF - T-Bar Plaster Frame XG-LIPF - Lay-In Plaster Frame		<ul style="list-style-type: none"> • Available Sizes Only as Listed • Steel Frame and Cores • Units Available with Multiple Cores depending on Neck Size


All Dimensions ±1/16"

Model: XG-9000S-9 Louvered Face - Modular Core - Bolt Slot

XG-9000S-9 - Bolt Slot




Side View



Available Module Size
24 x 24

Front View



1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Finish 24 Mill Finish Optional Finish 02 Satin Silver 03 Black 28 Custom Color	XG-OBDA - Steel Opposed Blade Damper XG-OBDA - Aluminum OBD XG-L9 - Equalizing Grid (Sq / Rect) XG-TR - Transition Square to Round XG-TR - Deep Transition XG-PF - Plaster Frame XG-TBPF - T-Bar Plaster Frame XG-LIPF - Lay-In Plaster Frame		<ul style="list-style-type: none"> • Available Sizes Only as Listed • Steel Frame and Cores • Units Available with Multiple Cores depending on Neck Size

All Dimensions ±1/16"