



Model: XG-7500 FRS-6

Face Mounted Pattern Controller - Perforated Face - Lay In T-Bar


XG-7500 FRS-6 - Lay in T-Bar



Listed Size
Nominal
Face
24 x 24

Available
Round Inlets
6
8
10
12
14
16

Face View





1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
<p>Standard Finish:</p> <ul style="list-style-type: none"> 01 White <p>Optional Finish:</p> <ul style="list-style-type: none"> 02 Satin Silver 03 Black 22 BBP - Black Backpan White Face 28 Custom Color 			<ul style="list-style-type: none"> • Steel Construction (Standard) • Sizes Available only as listed • Available only in Lay In T-Bar 24" x 24" • Face is Hinged • Fuse Links 165° Standard

All Dimensions ±1/16"


Model: XG-7500 FRSA-6 Face Mounted Pattern Controller - Adjustable Damper - Perforated Face - Lay In T-Bar

XG-7500 FRSA-6 - Lay in T-Bar



Listed Size
Nominal
Face
24 x 24

Available
Round Inlets
6
8
10
12
14
16





1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Optional Finish: 02 Satin Silver 03 Black 22 BBP - Black Backpan White Face 28 Custom Color			<ul style="list-style-type: none"> • Steel Construction • Sizes Available only as listed • Available only in Lay In T-Bar 24" x 24" • Face is Hinged • Fuse Links 165° Standard

All Dimensions ±1/16"

Model: XG-7500DF FRS-6 Face Mounted Pattern Controller - Perforated Drop Face - Lay In T-Bar


XG-7500DF FRS-6 - Lay in T-Bar



Listed Size
Nominal
Face
24 x 24

Available
Round Inlets
6
8
10
12
14
16

Face View





1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Optional Finish: 02 Satin Silver 03 Black 22 BBP - Black Backpan White Face 28 Custom Color			<ul style="list-style-type: none"> • Steel Construction (Standard) • Sizes Available only as listed • Available only in Lay In T-Bar 24" x 24" • Face is Hinged • Fuse Links 165° Standard

All Dimensions ±1/16"

Model: XG-7500DF FRSA-6 Face Mounted Pattern Controller - Adjustable Damper - Perforated Drop Face - Lay In T-Bar


XG-7500DF FRSA-6 - Lay in T-Bar



Overall Diffuser = Listed Size - $\frac{1}{4}$

Listed Size
Nominal
Face
24 x 24

Available
Round Inlets
6
8
10
12
14
16



1. Available Finishes	2. Available Accessories	3. Available Options	4. Construction Details
Standard Finish: 01 White Optional Finish: 02 Satin Silver 03 Black 22 BBP - Black Backpan White Face 28 Custom Color			<ul style="list-style-type: none"> Steel Construction (Standard) Sizes Available only as listed Available only in Lay In T-Bar 24" x 24" Face is Hinged Fuse Links 165° Standard

All Dimensions $\pm 1/16"$