



QWIK SHIP

EXPRESS LEAD TIME STANDARD PRODUCTS

Airolite’s Qwik Ship program includes a comprehensive portfolio of products and a broad selection of options and finish selections, ensuring on-time and on-budget results with “The Look that Works.” Contact your local Airolite representative to determine how Airolite’s Qwik Ship program can support your most demanding project completion schedules.

Best Available
Manufacturing Lead Time

MILL FINISH PAINTED FINISH



Miami-Dade County Qualified & Florida Code Approved Louvers

Drainable, Sightproof, and Storm Class Louvers
Extruded aluminum with mechanically fastened construction

MIAMI-DADE COUNTY QUALIFIED:		
K8206AMD, K6746MD, K6746MDE, SCH601MD, SCH601MDE	5 DAY	10 DAY
SCV302MD, SCV501MD, SCV660MD, SCC550MD, SCC901MD		
FLORIDA CODE APPROVED:		
K6746X	5 DAY	10 DAY

AMCA Licensed air performance and water penetration ratings (K8206AMD, K6746MD, K6746MDE, K6746X)
AMCA Licensed air performance, water penetration and wind-driven rain ratings (SCH601MD, SCH601MDE, SCV302MD, SCV501MD, SCV660MD, SCC550MD, SCC901MD)



Storm Class™ Louvers

Designed and rated to provide high volume intake and exhaust ventilation and prevent water penetration under wind-driven rain conditions
Extruded aluminum with mechanically fastened construction

HORIZONTAL BLADES:		
SCH201, SCH401, SCH501, SCH601	1 DAY	5 DAY
SCC901, SCC550	5 DAY	10 DAY
VERTICAL BLADES:		
SCV302, SCV501	1 DAY	5 DAY

AMCA Licensed air performance, water penetration, and wind-driven rain ratings



Adjustable and Combination Louvers

Adjustable blades open for controlled ventilation or closed to restrict air leakage and water penetration
Combination louvers yield constant appearance with adjustable blade control and versatility

EXTRUDED ALUMINUM ADJUSTABLE:		
T6796, T6732W, T6636	3 DAY	5 DAY
EXTRUDED ALUMINUM COMBINATION:		
K8204, K8206, K8504, K8506, K8206A	3 DAY	5 DAY

AMCA Licensed air performance and water penetration ratings (T6796, T6732W, K8204, K8206, K8504, K8506, K8206A)
AMCA Licensed air performance rating (T6636)



Stationary Louvers

Visible or concealed mullions
Extruded aluminum with mechanically fastened construction

EXTRUDED ALUMINUM:

K604	1 DAY	5 DAY
------	-------	-------

AMCA Licensed air performance and water penetration ratings



Drainable Louvers

Visible or concealed mullions
Extruded aluminum with mechanically fastened construction

EXTRUDED ALUMINUM:

K609HP, K6744, K6746, K6746HP	1 DAY	5 DAY
-------------------------------	-------	-------

AMCA Licensed air performance and water penetration ratings



Narrow Profile Louvers

Visible or concealed mullions
Extruded aluminum with mechanically fastened construction

EXTRUDED ALUMINUM:

K6772	1 DAY	5 DAY
-------	-------	-------

AMCA Licensed air performance and water penetration ratings



Sightproof Louvers

Visible or concealed mullions
Drainable or non-drainable blade configurations
Extruded aluminum with mechanically fastened construction

EXTRUDED ALUMINUM:

K605D	1 DAY	5 DAY
K605	5 DAY	10 DAY

AMCA Licensed air performance and water penetration ratings

ACCESSORIES, OPTIONS and FINISHES

Adding accessories may increase lead time

Accessories and Options:

Birdscreens (Internal Only)

- Flattened expanded and wire mesh aluminum
- Wire cloth galvanized and stainless

Insect Screens - Aluminum (Internal Only)

Blank-Off Panels

- 0.032 in. (1 mm) aluminum, 1 in. (25 mm) and 2 in. (50 mm) insulated blank-off panels, finished black on exterior only
- 0.050 in. (2 mm) aluminum non-insulated blank-off panels, finished black on exterior only

Clip and Continuous Angles

Exterior Flanges

- 1.5 in. (38 mm) flange
- 2.0 in. (50.8 mm) flange
- 5.0 in. (127 mm) flange

Sill Flashing

Mechanically Fastened Construction

Finishes:

- Standard Kynar 500® finishes
- Standard fluoropolymer finishes
- Standard Kynar 500® pearlescent finishes
- Standard anodize finishes - color and clear
- Custom color Kynar 500®



Qwik Ship lead times may vary slightly depending on availability of options and accessories.

Custom colors are defined as in-house blends of baked enamel and Kynar 500® only. Reference Airo-lite's Finishes & Colors brochure.
Note: Express Qwik Ship lead times commence upon receipt of color approval.