








Product Features:



- Perforated diffusers provide a smooth continuous ceiling aesthetic
- Face mounted pattern deflectors enable optimal mixing
- Deflectors can be adjusted to change airflow pattern
- Utilizes a hinged and fully removable face panel for easy cleaning
- Available in steel, aluminum, aluminum face and drop face applications
- Available with round or square neck inlets
- Multiple border styles available for various ceiling applications
- Face panel uses 51% free area perforated metal

Finishes

| | | |
|-------------------------|------------------------------|--|
| 01 - White ¹ | 03 - Black | ¹ White Finish is suitable for a primer coat if field painting is required. |
| 02 - Satin Silver | 24 - Mill | |
| 28 - Custom Color | 22 - BBP | |
| | Black Back Pan White Face | |


CFD Throw Pattern Visualization

Optional Accessories:

-  TBPF - T-Bar Plaster Frame
-  2"BC - 2" Beaded Inlet Collar
-  BDS - Butterfly Damper
-  L9 - Equalizing Grid (Square / Rect)
G3 - Equalizing Grid (Round)
-  RSD - Radial Shutter Damper
-  EQS - Earthquake Straps
-  FGBP - Fiberglass Backpan








Side View


| Listed Size |
|-------------|
| Nominal |
| Face |
| 24 x 24 |
| 12 x 12 |




Face View

| Air Pattern Options | | | | |
|---|---|---|--|---|
| 1 Way | 2 Way Corner | 2 Way | 3 Way | 4 Way |
|  |  |  |  |  |


Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.



Side View








| Listed Size |
|-------------|
| Nominal |
| Face |
| 24 x 24 |
| 12 x 12 |




Face View


Overall Face = Nominal Face - $\frac{1}{4}$

| Air Pattern Options | | | | |
|---|---|---|--|---|
| 1 Way | 2 Way Corner | 2 Way | 3 Way | 4 Way |
|  |  |  |  |  |


Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.








Side View




| Listed Size |
|-------------|
| Nominal |
| Face |
| 24 x 24 |
| 12 x 12 |








Face View

| Air Pattern Options | | | | |
|---|---|---|--|---|
| 1 Way | 2 Way Corner | 2 Way | 3 Way | 4 Way |
|  |  |  |  |  |

Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.



| Air Pattern Options | | | | |
|---|---|---|--|---|
| 1 Way | 2 Way Corner | 2 Way | 3 Way | 4 Way |
|  |  |  |  |  |

Note: This product complies with NFPA 90A-18 standard 4.3.7.3.2 and 4.3.8.3.2 and is constructed with openings through which a 1/2" sphere can not pass.