












**Multiple Sections**

Height > 96 1/2 ≤ 144 1/2



## Single Section




### Structure Depth

- Min. structure depth 4 in.
- Max. structure depth 10.5 in. (12 in. sleeve)
- Max. structure depth 14.5 in. (16 in. sleeve)

# Multiple Sections

Height ≤ 96 1/2




**Structure Depth**

- Min. structure depth 4 in.
- Max. structure depth 11.5 in.

## Multiple Sections

Height > 96 1/2 ≤ 144 1/2



### Structure Depth

- Min. structure depth 4 in.
- Max. structure depth 13.25 in.

## Our Commitment

As a result of our commitment to continuous improvement, Greenheck reserves the right to change specifications without notice.

Product warranties can be found online at [Greenheck.com](http://Greenheck.com), either on the specific product page or in the literature section of the website at [Greenheck.com/Resources/Library/Literature](http://Greenheck.com/Resources/Library/Literature).

