

## Application

Model FD-150 is a static rated fire damper approved for use in floors, walls, and partitions with fire resistance ratings less than 3 hours. This model carries a 1½ hour UL fire damper label. UL 555 classifies static rated fire dampers for use in HVAC systems that are automatically shut down in the event of fire.

## Ratings

### UL 555 Fire Resistance Rating

Fire Rating: 1½ hours

## Construction

	Standard	Optional
<b>Frame Material</b>	Galvanized steel*	-
<b>Frame Depth</b>	3 <sup>11</sup> / <sub>16</sub> in. (94mm)	-
<b>Blade Material</b>	Galvanized steel*	-
<b>Closure Spring</b>	Stainless steel	-
<b>Fusible Link</b>	165°F (74°C)	212°F (100°C)
<b>Mounting</b>	Vertical	Horizontal

\* in gauges required by UL listing R13317



\* These dimensions are furnished approximately ¼ in. (6mm) undersize.



See complete marking on product.  
UL 555 Classification R13317

Model FD-150 meets the requirements for fire dampers established by:

**National Fire Protection Association**

NFPA Standards 80, 90, & 101



**International Building Code (IBC)**

**California State Fire Marshall (CFSM)**

Listing #3225-981:105 for use in walls

**Underwriters Laboratories Standard 555**

(Listing R13317)



## Options and Accessories

---

- POC retaining angles
- Transitions: (A, B)

## Document Links

---

[Installation Instructions](#)



[Life Safety Damper Catalog](#)



[Damper Product Selection Guide](#)



[Specifications](#)




## Factory Sleeve Option FD-150

All fire damper installations require the use of sleeves, angles and methods described in the installation instructions. Sleeves can be field fabricated or factory furnished as a completed damper/sleeve assembly.

Sleeves are galvanized steel and are available in 20 through 16 ga. (1mm - 1.5mm) thicknesses and lengths up to 36 in. (914mm).

“K” dimension specifies location of damper within the sleeve. Minimum is 4 in. (102mm), maximum is “L” less 4 in. (102mm), which allows for mounting angle installation, and duct connection at each end of the sleeve. If “K” dimension is not specified, it will be provided as one half of “L” dimension (damper centered in sleeve).

**Note: If using access doors, the door should be installed on the “K” side of the damper.**




# Type A

Dampers larger than maximum single section size are supplied in two or more sections of equal size. Multi-section dampers are factory assembled ready for installation.

## Size Limitations


Inches (mm)	Type A		Type B	
	Minimum	Maximum	Minimum	Maximum
<b>Single Section Vertical</b>	4 x 4 (102 x 102)	48 x 48 (1219 x 1219)	4 x 3 (102 x 76)	48 x 42 (1219 x 1067)
<b>Multi Section Vertical*</b>	NA	96 x 48, 74 x 74 or 120 x 40 (2438 x 1219, 1880 x 1880 or 3048 x 1016)	NA	96 x 42, 74 x 69 or 120 x 35 (2438 x 1067, 1880 x 1753 or 2048 x 889)
<b>Single Section Horizontal</b>	4 x 4 (102 x 102)	48 x 48 (1219 x 1219)	4 x 3 (102 x 76)	48 x 36 (1219 x 914)
<b>Multi Section Horizontal*</b>	NA	96 x 48 or 120 x 40 (2438 x 1219 or 3048 x 1016)	NA	96 x 42 or 120 x 35 (2438 x 1067 or 3048 x 889)

\*Consult factory for number of sections.




\* These dimension are furnished approximately 1/4 in. (6mm) undersize.


① **Maximum Single Section Dimensions**



② **Multi-Section Limitations**  
Maximum height is 48 in. (1219mm) when width is 96 in. (2438mm) or less.




③ **Multi-Section Limitations**  
Maximum height is 74 in. (1880mm) when width is less than or equal to 74 in. (1880mm). (Vertical mullion provided on dampers over 37 in. (940mm) wide and 48 in. (1219mm) high.



# Type B



Dampers larger than maximum single section size are supplied in two or more sections of equal size. Multi-section dampers are factory assembled ready for installation.

① Maximum Single Section Dimensions



② Multi-Section Limitations

Maximum height is 42 in. (1067mm) when width is 96 in. (2438mm) or less



Type B

H*	O*	H*	O*
3 (76)	5 (127)	37 (940)	42 (1067)
4 (102)	6 (152)	38 (965)	44 (1118)
5 (127)	7 (178)	39 (991)	45 (1143)
6 (152)	8 (203)	40 (1016)	46 (1168)
7 (178)	9 (229)	41 (1041)	47 (1194)
8 (203)	10 (254)	42 (1067)	48 (1219)
9 (229)	11 (279)	43 (1092)	49 (1245)
10 (254)	12 (305)	44 (1118)	49 (1245)
11 (279)	13 (330)	45 (1143)	49 (1245)
12 (305)	14 (356)	46 (1168)	50 (1270)
13 (330)	15 (381)	47 (1194)	51 (1295)
14 (356)	16 (406)	48 (1219)	52 (1321)
15 (381)	18 (457)	49 (1245)	53 (1346)
16 (406)	19 (483)	50 (1270)	54 (1372)
17 (432)	20 (508)	51 (1295)	55 (1397)
18 (457)	21 (533)	52 (1321)	56 (1422)
19 (483)	22 (559)	53 (1346)	57 (1448)
20 (508)	23 (584)	54 (1372)	58 (1473)
21 (533)	24 (610)	55 (1397)	59 (1499)
22 (559)	26 (660)	56 (1422)	60 (1524)
23 (584)	27 (686)	57 (1448)	61 (1549)
24 (610)	28 (711)	58 (1473)	62 (1575)
25 (635)	29 (737)	59 (1499)	63 (1600)
26 (660)	30 (762)	60 (1524)	64 (1626)
27 (686)	31 (787)	61 (1549)	65 (1651)
28 (711)	32 (813)	62 (1575)	66 (1676)
29 (737)	33 (838)	63 (1600)	67 (1702)
30 (762)	34 (864)	64 (1626)	68 (1727)
31 (787)	36 (914)	65 (1651)	70 (1778)
32 (813)	37 (940)	66 (1676)	71 (1803)
33 (838)	38 (965)	67 (1702)	72 (1829)
34 (864)	39 (991)	68 (1727)	73 (1854)
35 (889)	40 (1016)	69 (1753)	74 (1880)
36 (914)	41 (1041)		

All multiple section dampers with B transitions, will include a factory installed sleeve.

\* Dimension in inches (mm). These dimensions are furnished ¼ in. (6mm) undersize. (All 'H' dimensions larger than 43 in. (1092mm) are two sections high. The bottom section is a Type A and the top section is a Type B.)

