

Application

Models HBS-330 and HBS-331 are heavy duty double flanged channel frame style dampers with double thickness fabricated airfoil blades. They are designed to protect against rapid pressure changes due to an explosion. Qualified to pressures as high as 5.77 psi covers many applications in Unified Facilities Criteria (UFC) and General Services Administration (GSA) codes and standards, including Charge Weight II at 82 feet.

Ratings

Pressure

1.5 - 5.77 psi (42-160 in. wg)
 (10 - 40 kPa) blast load
 Consult factory for lower pressures

Velocity

Up to 4000 fpm (20.3 m/s)

Temperature

Minimum: -40°F
 Maximum: 250°F (121°C)

Size Limitations

W x H	Minimum Size	Maximum Size	
		Single Section	Two Sections*
Inches	6 x 6	36 x 96	77 x 96
mm	152 x 152	914 x 2438	1956 x 2438

* Includes 5 in. (127mm) vertical mullion with removable cover plate

Code	Blast Loading
GSA- Level C	4 psi @ 28 psi-msec
UFC 4-010-01 (charge weight I at 148 ft)	4.76 psi @ 41.1 psi-msec
UFC 4-010-01 (charge weight II at 82 ft)	5.77 psi @ 29.69 psi-msec

1. Charge weight I = large mass explosion as would be found in a vehicle bomb - specific explosive weights are for US Government "For official use only" clearance personnel.
2. Charge weight II = medium size mass explosions as would be found in a briefcase or backpack bomb - specific weights are for US Government "For official use only" clearance personnel.



Note: Spring Location is determined from the perspective of viewing the damper with the blast coming towards you/facing the blast. As shown: HBS-330 left; HBS-331 right.

Options Available:


- Bolt holes in flanges

Construction

Construction	Standard	Optional
Frame Material	Galvanized steel	304SS, 316SS, Carbon Steel
Frame Material Thickness	10 ga. (3.5mm)	-
Frame Type	Flanged Channel	-
Frame Depth	10 in. (254mm)	-
Blade Material	Galvanized steel	304SS, 316SS, Galvaneal
Blade Type	Airfoil	-
Blade Thickness	16 ga. (1.6mm)	-
Axle Diameter	3/4 in. (19mm)	-
Axle Material	Plated steel	303SS, 316SS
Axle Bearings	External ball	-
Blade Seal	None	EPDM, Silicone
Linkage Material	Plated steel	304SS, 316SS
Flange Width	2 in. (51mm)	-
Springs	301SS	-
Spring Location	Right	Left, Both Sides
Finish	None	Hi Pro Polyester, Epoxy, Industrial Epoxy
Air Flow	Horizontal	Vertical Up or Vertical Down
Mounting Holes	None	Standard, Standard w/Corner Holes

Document Links


[Installation Instructions](#)



[Heavy Duty and Industrial Damper Catalog](#)



[Heavy Duty and Industrial Damper Selection Guide](#)



[All Damper Product Selection Guide](#)



[Specifications](#)



[Damper Warranty Statement](#)



Performance

Pressure Drop Data

This pressure drop data was conducted in accordance with AMCA Standard 500 using the three configurations shown. All data has been corrected to represent standard air at a density of 0.075 lb/ft³ (1.2 kg/m³).

Actual pressure drop found in any HVAC system is a combination of many factors. This pressure drop information along with an analysis of other system influences should be used to estimate actual pressure losses for a damper installed in a given HVAC system.

AMCA Test Figures

Figure 5.3 Illustrates a fully ducted damper. This configuration has the lowest pressure drop of the three test configurations because entrance and exit losses are minimized by straight duct runs upstream and downstream of the damper.

Figure 5.2 Illustrates a ducted damper exhausting air into an open area. This configuration has a lower pressure drop than Figure 5.5 because the entrance losses are minimized by a straight duct run upstream of the damper.

Figure 5.5 Illustrates a plenum mounted damper. This configuration has the highest pressure drop because of the high entrance and exit losses due to the sudden changes of area in the system.

Leakage Data

Leakage testing was conducted in accordance with AMCA Standard 500 and is expressed as cfm/ft² of damper face area. All data has been corrected to represent standard air at a density of 0.075 lb/ft³ (1.2 kg/m³).




Fig. 5.3




Fig. 5.2






Fig. 5.5 AMCA Test Figures




Bolt Hole Limitations

Bolt holes are available as an option. The standard pattern is $\frac{7}{16}$ in. (11mm) diameter holes (M dimension) spaced 6 in. (152mm) on center (L dimension). Custom bolt hole patterns are available. Contact factory for the limitations.




Standard Mounting Hole Pattern
Typical for single or double wide panel




Standard Mounting Hole Pattern with Corner Holes
Typical for single or double wide panel

HBS-330 and HBS-331 Difference



Model HBS-330

This model closes in the same direction as normal flow.



Model HBS-331

This model closes in the opposite direction as normal flow.

Note: Spring Location is determined from the perspective of viewing the damper in the blast coming towards you/facing the blast. As shown: HBS-330 left; HBS-331 right.