

All New!

Blowers Models USF & CSW

Greenheck's is pleased to introduce a new tiered blower product offering to provide the best value for your application with added flexibility. Your fan can now be delivered faster with Greenheck's new expedited delivery programs including 5 and 10 day Quick Build programs, and 15 day Fast Pass on common fan configurations without a price impact.

Greenheck's new tiered products and pricing structure ensures the greatest value for your needs.



USF-200

The USF-200 is a galvanized utility set fan that provides the best value for Class I airflow and pressure applications.



USF-300

The USF-300 offers a painted solution for Class I airflow and pressure applications. This model replaces our models SWB-200 and 300 series.



USF-400

The USF-400 is a new utility set series that spans the gap between traditional utility sets and industrial blowers. This series offers up to Class II performance capabilities with backward inclined or airfoil wheel options.



CSW

The CSW series is designed for high-end commercial and industrial applications. It is capable of Class IV airflow and pressures. This model replaces models BISW and AFSW.

Greenheck's New Blower Offerings

The models USF and CSW have multiple levels of construction to provide the best value for the intended application and performance.

For additional information on selecting the best fan for your application, contact the CVI team at cvifans@greenheck.com or call 888-284-3306.

USF-200



NEW OFFERING

Up to 13,700 cfm
5 in. wg
Class I
Arr 10

Sizes 6-22
BI Riveted Wheel

Permalock
Galvanized Scroll

Bolted Galvanized
Construction

Set Screw Bearings

Wheel Balanced

USF-300



**REPLACING
SWB 200 & 300**

Up to 54,000 cfm
5 in. wg
Class I
Arr 10

Sizes 6-49
BI Riveted Wheel

Permalock or Welded
Painted Scroll

Bolted Painted
Construction

Set Screw Bearings

Wheel Balanced

USF-400



NEW OFFERING

Up to 69,000 cfm
9 in. wg
Class II
Arr 10

Sizes 7-49
BI Riveted Wheel

Permalock or Welded
Painted Scroll

Welded Painted
Construction

Set Screw Bearings

Wheel Balanced

CSW



**REPLACING
BISW & AFSW**

Up to 220,000 cfm
22 in. wg
Class IV
Arr 1, 3, 4, 8, 9, 10

Sizes 7-73
BI or AF Wheel

Permalock or Welded
Painted Scroll

Welded Painted
Construction

Concentric Mount
Bearings

Full Factory
Vibration Test
AMCA 204

