

SERIES XG-7500 PERFORMANCE DATA

Module	Neck Size	<i>fpm Neck Velocity</i>	300	400	500	600	700	800	1000	1200	
		<i>Pv</i>	.006	.010	.016	.022	.031	.040	.062	.090	
12 x 12	6	CFM	60	80	100	120	135	155	195	235	
		Pt	.011	.019	.030	.043	.054	.072	.114	.165	
		NC	<15	<15	<15	17	21	25	31	36	
		Throw	4-Way*	1-2-3	1-2-5	2-3-5	2-3-6	3-4-6	3-4-6	4-5-7	5-6-8
			4-Way	1-2-4	1-2-5	2-3-6	2-4-6	3-4-7	3-5-7	4-6-8	5-6-9
			3-Way	1-2-4	1-3-5	2-3-6	3-4-6	3-5-7	4-5-7	4-6-8	5-6-9
			2-Way	1-2-5	2-3-5	3-4-6	3-5-6	4-5-7	4-5-7	5-6-8	5-6-9
	1-Way		1-2-5	2-3-5	3-4-6	3-5-7	4-5-7	4-5-8	5-6-8	5-7-9	
	8	CFM	105	140	175	210	245	280	350	420	
		Pt	.015	.027	.043	.061	.083	.109	.170	.245	
		NC	<15	<15	<15	20	25	30	37	43	
		Throw	4-Way*	1-2-5	2-3-6	3-4-7	3-5-7	4-5-8	4-6-9	5-7-10	6-7-11
			4-Way	1-2-5	2-3-6	3-4-7	3-5-8	4-6-9	4-6-9	5-7-11	6-8-12
			3-Way	1-2-5	2-4-7	3-5-8	4-5-8	4-6-9	5-7-10	6-8-11	7-8-12
2-Way			2-3-6	3-4-7	4-5-8	4-6-9	5-7-9	6-7-10	6-8-11	7-9-12	
1-Way	2-3-6		3-4-7	4-5-8	4-6-9	5-7-9	6-7-10	7-8-11	7-9-12		
24 x 24	6	CFM	60	80	100	120	135	155	195	235	
		Pt	.010	.019	.029	.042	.053	.070	.110	.160	
		NC	<15	<15	<15	17	21	25	31	36	
		Throw	4-Way*	1-2-4	1-2-5	2-3-5	2-4-6	3-4-6	3-5-7	4-5-8	5-6-8
			4-Way	1-2-4	1-3-5	2-3-6	3-4-7	3-4-7	3-5-7	4-6-8	5-6-9
			3-Way	1-2-4	1-3-5	2-4-6	3-4-7	3-5-7	4-5-8	5-6-8	5-7-9
			2-Way	1-3-5	2-3-6	3-4-6	3-5-7	4-5-7	4-5-8	5-6-9	5-7-9
	1-Way		1-3-5	2-3-6	3-4-6	3-5-7	4-5-7	4-6-8	5-6-9	6-7-10	
	8	CFM	105	140	175	210	245	280	350	420	
		Pt	.016	.028	.043	.063	.085	.111	.174	.250	
		NC	<15	<15	<15	20	25	30	37	43	
		Throw	4-Way*	1-2-5	2-3-6	3-4-7	3-5-8	4-6-9	4-6-9	5-7-10	6-8-11
			4-Way	1-2-5	2-3-7	3-4-8	3-5-9	4-6-9	4-7-10	6-8-11	7-9-12
			3-Way	1-2-6	2-4-7	3-5-8	4-6-9	4-7-10	5-7-10	6-8-11	7-9-12
2-Way			2-3-6	3-5-7	4-6-8	5-6-9	5-7-10	6-7-10	7-8-12	7-9-13	
1-Way	2-3-7		3-5-8	4-6-8	5-7-9	5-7-10	6-8-11	7-8-12	8-9-13		

CEILING
DIFFUSERS

PERFORATED
CEILING DIFFUSERS

XG-7500/XG-7550

SERIES XG-7500 PERFORMANCE DATA

Module	Neck Size	<i>fpm Neck Velocity</i>	300	400	500	600	700	800	1000	1200	
		<i>Pv</i>	.006	.010	.016	.022	.031	.040	.062	.090	
24 x 24	10	CFM	165	220	275	325	380	435	545	655	
		Pt	.023	.041	.064	.090	.123	.161	.252	.365	
		NC	<15	<15	15	22	28	33	42	48	
		Throw	4-Way*	1-3-6	2-4-8	3-5-9	4-6-10	5-7-11	5-8-11	7-9-13	8-10-14
			4-Way	1-3-6	2-4-8	3-5-10	4-6-11	5-7-12	5-8-12	7-10-14	8-11-15
			3-Way	1-3-7	2-5-9	3-6-10	5-7-1	5-8-12	6-9-13	8-10-14	9-11-16
			2-Way	2-4-8	4-6-9	5-7-10	6-8-11	7-9-12	7-9-13	8-10-14	9-11-16
			1-Way	2-4-8	4-6-9	5-7-11	6-8-11	7-9-12	7-9-13	9-11-15	9-12-16
		12	CFM	235	315	395	470	550	630	785	940
			Pt	.025	.044	.070	.099	.135	.177	.275	.395
	NC		<15	<15	17	24	31	37	45	52	
	Throw		4-Way*	1-3-7	3-5-10	4-6-11	5-7-12	6-8-13	6-10-14	8-11-15	10-12-17
			4-Way	1-3-7	3-5-10	4-6-12	5-7-13	6-9-14	7-10-15	8-12-17	10-13-18
			3-Way	1-3-8	3-6-11	4-7-12	6-8-13	7-10-14	8-11-15	9-12-17	11-13-19
			2-Way	3-5-9	5-7-11	6-8-12	7-9-13	8-10-15	9-11-16	10-12-17	11-13-19
			1-Way	3-5-10	5-7-11	6-8-13	7-10-14	8-11-15	9-11-16	10-13-18	11-14-20
	14		CFM	320	430	535	640	750	855	1070	1285
			Pt	.033	.059	.091	.131	.179	.233	.365	.527
		NC	<15	<15	18	27	34	41	50	56	
		Throw	4-Way*	2-4-8	3-6-11	5-7-13	6-8-14	7-10-15	7-11-16	9-13-18	11-14-20
			4-Way	2-4-9	3-6-12	5-7-14	6-8-15	7-10-16	8-12-17	10-14-19	12-15-21
			3-Way	2-4-10	3-7-13	5-8-14	7-10-15	8-12-17	9-13-18	11-14-20	13-15-22
			2-Way	3-6-11	5-8-13	7-10-14	8-11-16	9-12-17	10-13-18	12-14-20	13-16-22
			1-Way	3-6-11	5-8-13	7-10-15	8-11-16	9-12-17	10-13-19	12-15-21	13-16-23
		16	CFM	420	560	700	840	975	1115	1395	1675
			Pt	.040	.071	.110	.159	.214	.280	.438	.631
	NC		<15	<15	20	29	36	43	52	60	
	Throw		4-Way*	2-4-10	4-6-13	5-8-14	6-10-16	7-11-17	8-13-18	11-14-20	13-16-22
4-Way			2-4-10	3-7-13	5-8-16	7-10-17	8-12-19	9-13-20	11-16-22	13-17-24	
3-Way			2-4-11	3-8-14	5-9-16	8-11-18	9-13-19	10-14-20	13-16-23	14-18-25	
2-Way			4-7-13	6-9-15	8-11-16	9-13-18	10-14-19	12-15-21	13-16-23	15-18-25	
1-Way			4-7-13	6-9-15	8-11-17	9-13-18	10-14-20	12-15-21	14-17-24	15-18-26	

**CEILING
DIFFUSERS**
**PERFORATED
CEILING DIFFUSERS**
XG-7500/XG-7550