


ARC-24

A Reliable and Smart Low-Profile Condenser Fan

Greenheck's low-profile ARC condenser fan is the simple, smart, and reliable solution for prolonging the lifespan of your HVAC system. With speed controllability and a high-efficiency rating, model ARC keeps air moving to help regulate temperature and provide proper ventilation for your equipment.



Features and Benefits

- Air performance up to 7,100 cfm and 1.00 in. wg
- High efficiency galvanized steel propeller
- Electronically commutated (EC) motor with 0-10V speed control capabilities
- 60° C motor ambient temperature
- IP54 rated motor and tested under UL 705-Water Spray
- UL Recognized Motor
- Painted steel wire guard
- Optional factory mounted junction box


ARC-24 Condenser Fan

Construction Features



Fan Panel Material	Galvanized
Guard Material	Painted steel wire
Propeller Diameter (Typ.)	24 in.
Propeller Material	Galvanized steel
Number of Blades	7
Standard Warranty Length	1 year

EC Motor Information

Horsepower	1 hp
Voltage/Phase	208-230v/1 460v/1
Hertz (Cycle)	50/60 Hz
Motor Enclosure	TEAO
RPM Range	180-1,200 rpm
Full Load Amps	6.9-6.38A (208-230v/1) 3.58A (460v/1)




Dimensions



Height	Width	Depth
30 in.	30 in.	7 in.

Performance



For more information regarding the Greenheck ARC consult your local Greenheck sales representative.

