

**SERIES XG-CC45F PERFORMANCE DATA**  
**MODEL XG-CC45F**

Size	Duct Area ft <sup>2</sup>	Nk Vel	200	300	400	500	600	700	800	900	1000
		Ps	-.006	-.013	-.024	-.037	-.054	-.073	-.095	-.120	-.149
06x06	.25	CFM	46	69	92	115	138	161	184	207	230
		NC	-	-	-	-	-	14	18	22	26
08x06	.33	CFM	61	92	122	152	183	213	243	274	304
		NC	-	-	-	-	-	15	19	23	27
10x06	.42	CFM	77	115	154	192	230	268	307	345	383
		NC	-	-	-	-	11	16	20	24	28
08x08	.44	CFM	83	125	166	204	249	291	332	374	415
		NC	-	-	-	-	11	16	21	25	28
12x06	.50	CFM	92	139	185	232	279	325	372	418	465
		NC	-	-	-	-	12	17	21	25	29
16x06 12x08	.67	CFM	126	189	253	317	378	442	506	570	630
		NC	-	-	-	-	13	18	22	26	30
10x10	.69	CFM	131	196	261	327	392	457	522	588	653
		NC	-	-	-	-	13	18	22	26	30
12x10 20x06	.83	CFM	157	235	313	391	469	547	625	703	781
		NC	-	-	-	-	13	18	23	26	30
24x06 12x12	1.00	CFM	191	287	382	478	573	669	764	860	955
		NC	-	-	-	-	14	19	24	28	31
14x14	1.36	CFM	260	390	520	650	780	910	1040	1169	1299
		NC	-	-	-	-	15	20	25	29	32
18x12 36x06	1.50	CFM	287	430	573	717	860	1003	1146	1290	1433
		NC	-	-	-	-	16	21	25	29	33
18x16 24x12	2.00	CFM	382	573	764	955	1146	1337	1528	1719	1910
		NC	-	-	-	11	17	22	26	30	33
18x18	2.25	CFM	430	645	860	1075	1290	1505	1719	1934	2149
		NC	-	-	-	11	17	22	26	30	34
30x12	2.50	CFM	478	717	955	1194	1433	1672	1910	2149	2388
		NC	-	-	-	11	17	23	27	31	34
20x20	2.78	CFM	531	797	1062	1328	1593	1859	2124	2390	2655
		NC	-	-	-	12	18	23	27	31	35
24x18 36x12	3.00	CFM	573	860	1146	1433	1719	2006	2292	2579	2865
		NC	-	-	-	12	18	23	28	32	35
22x22	3.36	CFM	642	963	1284	1605	1926	2247	2568	2888	3209
		NC	-	-	-	12	18	23	28	32	35
48x12 24x24	4.00	CFM	768	1152	1536	1920	2304	2688	3072	3456	3840
		NC	-	-	-	13	19	24	29	33	36
48x18 36x24	6.00	CFM	1152	1728	2304	2880	3456	4032	4608	5184	5760
		NC	-	-	-	15	21	26	30	34	38

**CONTINUED**

**SERIES XG-CC45F PERFORMANCE DATA**  
**MODEL XG-CC45F**

Size	Duct Area ft <sup>2</sup>	Nk Vel	200	300	400	500	600	700	800	900	1000
		Ps	-.006	-.013	-.024	-.037	-.054	-.073	-.095	-.120	-.149
48x24 36x32	8.00	CFM	1536	2304	3072	3840	4608	5376	6144	6912	7680
		NC	-	-	-	16	22	27	31	35	39
48x36	12.00	CFM	2304	3456	4608	5760	6912	8064	9216	10368	11520
		NC	-	-	11	17	23	28	33	37	40
48x48	16.00	CFM	3072	4608	6144	7680	9216	10752	12288	13824	15360
		NC	-	-	12	18	24	29	34	38	41

**PERFORMANCE NOTES FOR SERIES XG-CC45F**

All data is tested in accordance with ANSI/ASHRAE 70-2006.

**DEFINITION OF UNITS**

CFM Cubic Feet per Minute (Air)

Velocity Neck Velocity of air stream in Feet Per Minute

Ps Negative Static pressure =  $P_t - P_v$  (inches of water column)

NC Noise criterion, Sound pressure level. NC ratings are based on sound power level (L<sub>w</sub>)

RE:  $10^{-12}$  watts minus a 10dB room attenuation in all octave bands.