



Dual Duct Air Terminal Unit
Short Mixing



The control panel will overhang the top and bottom of Dual Duct Air Terminal Units 4-6, 1" [25.4 mm].
Control Panel Mounting Surface width by height is 13 7/8" X 9 7/8"



Unit Size	Inlet Diameter		CFM MAX	Inlet Duct Length A		Unit Width W		Unit Height H		Unit Length L		Discharge Width B		Discharge Height C		Shipping Weight			
	Standard Both Ducts	Optional Hot Duct		In.	mm	In.	mm	In.	mm	In.	mm	In.	mm	In.	mm	In.	mm	lb	kg
4	4	-	300	10	254	20	508	10	254	22	559	8	203	6	152	30	14		
5	5	-	375	5	127	20	508	10	254	22	559	8	203	6	152	30	14		
6	6	-	540	5	127	20	508	10	254	22	559	8	203	6	152	30	14		
7	7	6	760	5	127	24	610	12 1/2	318	26	660	10	254	8	203	41	19		
8	8	6	990	5	127	24	610	12 1/2	318	26	660	10	254	8	203	41	19		
9	9	6,8	1250	5	127	28	711	12 1/2	318	30	762	12	305	10	254	50	23		
10	10	6,8	1640	5	127	28	711	12 1/2	318	30	762	12	305	10	254	50	23		
12	12	6,8,10	2350	5	127	32	813	15	381	34	864	14	356	12	305	62	28		
14	14	6,8,10,12	3250	5	127	36	914	17 1/2	445	38	965	17	432	14	356	84	38		
16	16	6,8,10,12,14	4100	5	127	40	1016	18	457	42	1067	20	508	15	381	100	45		

Standard Construction

- 1/2" Dual Density, Coated Fiberglass
- All Insulations Meet NFPA 90A And UL 181
- All Fiberglass Insulations Have Coated Edges To Prevent Fiber Migration
- Units Are Constructed With 22 Gauge Casing & Inlet Duct
- 18 Gauge Equivalent Damper Assembly With Integral Blade Seal
- Control Panel With Dust Cover
- 1:20 Mixing Efficiency
- Integral Mixing Attenuator
- Dual Inlet Airflow Sensor