


Dual Duct Air Terminal Unit
High Efficiency Mixing



The standard location for the control panels are Right Hand. Looking in the direction of airflow, the control panel is on the right.
The control panel will overhang the top and bottom of Dual Duct Air Terminal Units 4 - 6, 1" [25.4 mm] or 1 1/8" [21 mm] on Dual Duct Air Terminal Unit 8. Control Panel Mounting Surface width by height is 13 7/8" x 9 5/8"

Unit Size	Inlet Diameter		CFM MAX	Inlet Duct Length A		Unit Width W		Unit Height H		Unit Length L		Discharge Width B		Discharge Height C		Shipping Weight			
	Standard Both Ducts	Optional Hot Duct		In.	mm	In.	mm	In.	mm	In.	mm	In.	mm	In.	mm	In.	mm	lb	kg
4	4	-	300	10	254	20	508	10	254	40	1016	8	203	6	152	55	25		
5	5	-	375	5	127	20	508	10	254	40	1016	8	203	6	152	55	25		
6	6	-	540	5	127	20	508	10	254	40	1016	8	203	6	152	55	25		
7	7	6	760	5	127	24	610	12 1/2	318	48	1219	10	254	8	203	72	33		
8	8	6	990	5	127	24	610	12 1/2	318	48	1219	10	254	8	203	72	33		
9	9	6,8	1250	5	127	28	711	12 1/2	318	58	1473	12	305	10	254	94	43		
10	10	6,8	1640	5	127	28	711	12 1/2	318	58	1473	12	305	10	254	94	43		
12	12	6,8,10	2350	5	127	32	813	15	381	72	1829	14	356	12	305	120	55		
14	14	6,8,10,12	3250	5	127	36	914	17 1/2	445	72	1829	17	432	14	356	140	64		
16	16	6,8,10,12,14	4100	5	127	40	1016	18	457	72	1829	20	508	15	381	164	75		

Standard Construction		
<ul style="list-style-type: none"> • 1/2" Dual Density, Coated Fiberglass • All Insulations Meet NFPA 90A And UL 181 • All Fiberglass Insulations Have Coated Edges To Prevent Fiber Migration 	<ul style="list-style-type: none"> • Units Are Constructed With 22 Gauge Casing & Inlet Duct • 18 Gauge Equivalent Damper Assembly With Integral Blade Seal 	<ul style="list-style-type: none"> • Control Panel With Dust Cover • 1:30 Mixing Efficiency • Integral Mixing Attenuator Discharge Section • Dual Inlet Airflow Sensor