






Low Profile Series Fan Powered Air Terminal Unit



The standard location for control enclosure is Left Hand. Looking in the direction of airflow, the control enclosure is on the left

Case size 4 includes two discharge blowers

All Dimensions shown in inches parentheses () indicate millimeter



Optional Inlet Sizes 4,5 and 6. Available On Case Size 2 Only

Case Size	Inlet Size		Unit Width W	Unit Length		Unit Height		Induction			DISCHARGE				
	Standard			L	H	Width	Height	Loc.	Width	Height	A	B	C	D	E
2	8 (203) Round		23 (584)	39 (991)	11 (279)	10 1/2 (267)	8 1/2 (216)	9.5 (241)	9.5 (241)	7 (178)					
4	8 (203) x 16 (406) Rect.		42 (1067)	39 (991)	11 (279)	18 (457)	8 1/2 (216)	9 (229)	9 (229)	7 (178)					

PCS MOTOR CONFIGURATION	
Case Size	Horse Power
2	1/4
4	1/4 (QTY 2)

ECM MOTOR CONFIGURATION	
Case Size	Horse Power
2	1/3
4	1/3 (QTY 2)

Standard Construction

- 1/2" Dual Density, Coated Fiberglass
- All Insulations Meet NFPA 90A And UL181
- All Fiberglass Insulations Have Coated Edges To Prevent Fiber Migration
- Units are Constructed with 22 Gauge Casing and 18 Gauge Discharge
- 18 Gauge Equivalent Damper Assembly with Integral Blade Seal
- 18 x 10 Control Enclosure
- Optional Slip & Drive Discharge Connection
- Optional Induction Attenuator
- Inlet Airflow Sensor